NEW! Flyback Transformer ZD2087-AE



- Developed for use with the STMicroelectronics A/L6983I iso-buck converter
- Optimized for a 24 Vin solution with the evaluation board STEVAL-L6983IV1.
- 1500 Vrms, one minute isolation (hipot) between primary and secondary.
- AEC-Q200 (-40°C to +125°C)

Core material Ferrite Environment RoHS compliant, halogen free Terminations Tin-silver-copper over tin over nickel over phos bronze Weight 6.99 g Ambient temperature -40°C to +125°C Maximum part temperature +165°C (Ambient + temp rise) Storage temperature Component: -40°C to +125°C Tape and reel packaging: -40°C to +80°C Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Packaging 150 per 13″ reel Plastic tape: 44 mm wide, 0.5 mm thick, 28 mm pocket spacing, 14.6 mm pocket depth

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30 $^{\circ}\text{C}$ / 85% relative humidity)

Part number ¹	Inductance at 0 A ² ±10% (µH)	DCR (Oh pri	max ms) sec	Leakage inductance ³ max (µH)	Turns ratio pri : sec	Isolation ⁴ (Vrms)	Isat⁵ (A)	Output
ZD2087-AED	13.5	0.020	0.293	0.15	1 : 2.555	1500	8.0	30 V, 0.33 A

1. **Packaging: D** = 13" machine-ready reel. EIA-481 embossed plastic tape (150 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

- 2. Inductance is for the primary, measured at 500 kHz, 0.1 Vrms, 0 Adc.
- 3. Leakage inductance is for the primary with the secondary windings shorted.
- Shorted.
 1500 Vrms, one minute isolation (hipot) between primary and secondary.

DC current that causes the primary inductance to drop 30% from its value without current.

6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

L vs Current







 US
 +1-847-639-6400
 sales@coilcraft.com

 UK
 +44-1236-730595
 sales@coilcraft-europe.com

 Taiwan
 +886-2-2264
 3646
 sales@coilcraft.com.tw

 China
 +86-21-6218
 8074
 sales@coilcraft.com.cn

 Singapore
 + 65-6484
 8412
 sales@coilcraft.com.sg

Document 1786-1 Revised 02/16/24

© Coilcraft Inc. 2024 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information