

NEW!

Shielded Power Inductors – XGL1712



- Industry's lowest DCR and low power losses
- Wide inductance range up to 82 μ H
- High current handling with soft saturation characteristics
- AEC-Q200 (–40°C to +125°C) with 165°C max part temperature

Core material Composite**Core and winding loss** See www.coilcraft.com/coreloss**Environmental** RoHS compliant, halogen free**Terminations** RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.**Weight** 20 – 25 g**Operating voltage:** 0 – 60 V**Ambient temperature** –40°C to +125°C with (40°C rise) Irms current.**Maximum part temperature** +165°C (ambient + temp rise). [Derating](#).**Storage temperature** Component: –55°C to +165°C.

Tape and reel packaging: –55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Inductance ² ±20% (μ H)	DCR (mOhms) ³		SRF typ ⁴ (MHz)	Isat (A) ⁵			Irms (A) ⁶	
		typ	max		10% drop	20% drop	30% drop	20°C rise	40°C rise
XGL1712-102MED	1.0	0.9	1.1	27	40.0	68.0	95.0	40.0	55.0
XGL1712-162MED	1.6	1.1	1.3	21	32.0	54.5	77.0	36.0	50.0
XGL1712-232MED	2.3	1.3	1.5	17	28.5	48.0	69.5	31.6	43.5
XGL1712-332MED	3.3	1.6	1.9	15	23.0	40.0	59.0	30.3	41.7
XGL1712-472MED	4.7	2.0	2.3	13	19.9	35.0	51.5	27.2	37.7
XGL1712-562MED	5.6	2.5	2.8	12	18.2	32.0	47.0	24.6	33.9
XGL1712-752MED	7.5	3.1	3.6	9.7	16.5	28.5	42.0	22.4	31.5
XGL1712-103MED	10	3.8	4.4	8.4	14.3	24.5	35.0	20.3	27.9
XGL1712-153MED	15	6.3	7.2	6.6	11.3	19.7	29.0	16.8	22.7
XGL1712-183MED	18	6.9	7.9	6.3	10.9	18.5	27.0	15.4	21.2
XGL1712-223MED	22	8.8	9.8	5.7	9.8	16.6	24.0	14.4	19.5
XGL1712-333MED	33	13.7	15.2	5.1	8.9	14.6	20.5	11.3	15.4
XGL1712-473MED	47	18.7	20.7	4.1	7.1	11.8	16.5	9.7	13.3
XGL1712-683MED	68	28.2	31.3	3.4	5.6	9.2	12.8	8.1	11.0
XGL1712-823MED	82	34.6	38.4	2.8	5.3	8.8	12.5	7.1	9.7

1. When ordering, please specify **termination** code:**XGL1712-823MED****Termination:** **E** = RoHS compliant tin-silver over copper.**Special order:** **T** = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).**Packaging:** **D** = 13" machine-ready reel. EIA-481 embossed plastic tape (150 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

- Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
- DCR measured on a micro-ohmmeter.
- SRF measured using Agilent/HP 4395A or equivalent.
- DC current at 25°C that causes an inductance drop from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. [Click for temperature derating information](#).
- Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing

Irms testing was performed on 0.75 inch wide x 0.25 inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

www.coilcraft.com**US** +1-847-639-6400 sales@coilcraft.com**UK** +44-1236-730595 sales@coilcraft-europe.com**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw**China** +86-21-6218 8074 sales@coilcraft.com.cn**Singapore** + 65-6484 8412 sales@coilcraft.com.sg

Document 1754-1 Revised 02/17/23











© Coilcraft Inc. 2023

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



Shielded Power Inductors – XGL1712

Typical L vs Current








US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1754-2 Revised 02/17/23
 © Coilcraft Inc. 2023
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.






Shielded Power Inductors – XGL1712


Typical L vs Current



Typical L vs Frequency



* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0,13 mm



Recommended Land Pattern

Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Packaging 150/13" reel Plastic tape: 32 mm wide, 0.45 mm thick, 24 mm pocket spacing, 12.2 mm pocket depth



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1754-3 Revised 02/17/23
 © Coilcraft Inc. 2023
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.