









Shielded Power Inductors - XAL1080







- Industry's lowest DCR and low power losses
- · High current handling with soft saturation characteristics
- AEC-Q200 Grade 1 (-40°C to +125°C) with a 165°C max part temperature

Core material Composite

Core and winding loss See www.coilcraft.com/coreloss

Environmental RoHS compliant, halogen free

Terminations RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.

Weight 5.4 g

Operating voltage: 0 - 60 V

Ambient temperature -40°C to $+125^{\circ}\text{C}$ with $(40^{\circ}\text{C}$ rise) Irms current. **Maximum part temperature** $+165^{\circ}\text{C}$ (ambient + temp rise). Derating.

Storage temperature Component: -55°C to +165°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.

	Inductance ²	DCR (mOhms)3		SRF typ4	Isat (A) ⁵			Irms (A) ⁶	
Part number ¹	±20% (μH)	typ	max	(MHz)	10% drop	20% drop	30% drop	20°C rise	40°C rise
XAL1080-103MED	10	10.7	12.3	11.5	5.8	9.5	13.4	10.7	14.8
XAL1080-123MED	12	12.0	13.8	10.6	5.5	9.0	12.6	10.0	13.9
XAL1080-153MED	15	15.6	17.9	9.2	5.2	8.2	11.5	8.5	11.7
XAL1080-183MED	18	18.5	21.3	8.5	4.6	7.4	10.3	7.9	10.8
XAL1080-223MED	22	21.3	24.5	7.4	4.1	6.6	9.0	7.3	10.0
XAL1080-333MED	33	33.4	38.4	6.5	3.5	5.7	7.9	5.5	7.5

1. When ordering, please specify termination code:

XAL1080-333MED

Termination: E = RoHS compliant tin-silver over copper.

Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).

Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (500 parts per full reel). Quantities less than full reel qualitation in transport receipts reaching reac

tape (500 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

- 2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using Agilent/HP 4395A or equivalent.
- DC current at 25°C that causes an inductance drop from its value without current.
- Current that causes the specified temperature rise from 25°C ambient.
 This information is for reference only and does not represent absolute maximum ratings. Click for temperature derating information.
- 7. Electrical specifications at 25°C.


Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing

Irms testing was performed on 0.75 inch wide \times 0.25 inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

Typical L vs Frequency





US +1-847-639-6400 sales@coilcraft.com **UK** +44-1236-730595 sales@coilcraft-europe.com **Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw **China** +86-21-6218 8074 sales@coilcraft.com.cn

Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1766-1 Revised 05/15/23

© Coilcraft Inc. 2023

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.




Shielded Power Inductors - XAL1080











Typical L vs Current























Current (A)



Land Pattern

* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0,13 mm

Dimensions are in inches

Packaging 500/13" reel Plastic tape: 24 mm wide, 0.4 mm thick, 16 mm pocket spacing, 8.23 mm pocket depth

