



# Chip Inductors – 0603HC (1608)

With their high current ratings and ultra-small size, these chip inductors are ideal for today's high frequency, low voltage applications like mobile phones. They feature continuous current ratings up to 2.4 Amps DC and

will handle transient currents up to 50% higher. At low inductance values, their Q factors are also higher than our 0603CS Series.

Part number <sup>1</sup>	Inductance <sup>2</sup> (nH)	Percent tolerance <sup>3</sup>	Q min <sup>4</sup>	900 MHz		1.7 GHz		SRF min <sup>5</sup> (MHz)	DCR max <sup>6</sup> (Ohms)	Irms <sup>7</sup> (A)	Color code <sup>8</sup>
				L typ	Q typ	L typ	Q typ				
0603HC-1N6XJL_	1.6	<b>5</b>	24	1.67	49	1.65	63	12500	0.030	2.4	Black
0603HC-3N6XJL_	3.6	<b>5</b>	24	3.65	70	3.75	90	5900	0.048	2.3	Brown
0603HC-3N9XJL_	3.9	<b>5</b>	25	3.74	70	3.90	90	5900	0.054	2.2	Red
0603HC-6N8XJL_	6.8	<b>5</b>	35	6.72	70	7.10	75	5800	0.054	2.1	Orange
0603HC-7N5XJL_	7.5	<b>5</b>	38	7.33	70	7.90	68	3700	0.059	2.1	Yellow
0603HC-10NX_L_	10	<b>5,2</b>	38	9.70	73	10.5	57	3700	0.071	2.0	Green
0603HC-12NX_L_	12	<b>5,2</b>	38	12.3	68	14.5	41	3000	0.075	2.0	Blue
0603HC-15NX_L_	15	<b>5,2</b>	38	15.5	65	17.6	40	2800	0.080	1.9	Violet
0603HC-18NX_L_	18	<b>5,2</b>	40	19.5	62	25.0	40	2800	0.099	1.9	Gray
0603HC-22NX_L_	22	<b>5,2</b>	42	24.0	61	31.5	26	2400	0.099	1.8	White
0603HC-24NX_L_	24	<b>5,2</b>	42	25.8	55	35.0	21	2400	0.105	1.8	Black
0603HC-33NXJL_	33	<b>5</b>	47	34.3	50	—	—	1900	0.175	0.95	Brown
0603HC-47NXJL_	47	<b>5</b>	40	49.5	45	—	—	1530	0.195	0.85	Red

1. When ordering, specify **tolerance, termination and packaging** codes:

0603HC-24NXJLW

- Tolerance:** **G** = 2% **J** = 5% (Table shows stock tolerances in bold.)
- Termination:** **L** = RoHS compliant silver-palladium-platinum-glass frit.  
**E** = Halogen free component. RoHS compliant silver-palladium-platinum-glass frit terminations.  
 Special order: **T** = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).
- Packaging:** **W** = 7" machine-ready reel. EIA-481 punched paper tape (2000 parts per full reel).  
**U** = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter W instead.

- Inductance measured at 250 MHz using Coilcraft SMD-A fixture in Agilent/HP 4286 impedance analyzer with Coilcraft-provided correlation pieces.
  - Tolerances in bold are stocked for immediate shipment.
  - Q measured at 250 MHz using Agilent/HP 4291A with Agilent/HP 16193 test fixture.
  - SRF measured using Agilent/HP 8720D network analyzer and Coilcraft SMD-D test fixture.
  - DCR measured on micro-ohmmeter and Coilcraft CCF858 test fixture.
  - Current that causes a 20°C temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
  - Each part is marked with a single dot. The color dots are not unique identifiers and correspond to multiple inductance values.
  - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

**Designer's Kit C339** contains 10 of each of all 5% parts

**Core material** Ceramic

**Environmental** RoHS compliant, halogen free optional

**Terminations** RoHS compliant silver-palladium-platinum-glass frit.

**Weight** 3.3 – 3.7 mg

**Ambient temperature** –40°C to +125°C with Irms current

**Maximum part temperature** +145°C (ambient + temp rise).

**Storage temperature** Component: –40°C to +145°C.

Tape and reel packaging: –40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Temperature Coefficient of Inductance (TCL)** +25 to +125 ppm/°C

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Failures in Time (FIT) / Mean Time Between Failures (MTBF)**

One per billion hours / one billion hours, calculated per Telcordia SR-332

**Packaging** 2000 per 7" reel. Paper tape: 8 mm wide, 1.0 mm thick, 4 mm pocket spacing

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

**COILCRAFT** ACCURATE  
 REPEATABLE  
**PRECISION** MEASUREMENTS  
 SEE WEB SITE **TEST FIXTURES**

# HIGH CURRENT

## 0603HC (1608) Chip Inductors

**S-Parameter files**


ON OUR WEB SITE

**SPICE models**



ON OUR WEB SITE



### Typical Q vs Frequency



### Typical L vs Frequency



A	B	C	D	E	F	G	H	I	J
max	max	max	ref						
0.071	0.044	0.040	0.015	0.030	0.013	0.034	0.040	0.025	0.025
1,80	1,12	1,02	0,38	0,76	0,33	0,86	1,02	0,64	0,64

**Note:** Height dimension (C) is before optional solder application. For maximum height dimension including solder, add 0.006 in / 0,152 mm.



**US** +1-847-639-6400 sales@coilcraft.com  
**UK** +44-1236-730595 sales@coilcraft-europe.com  
**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw  
**China** +86-21-6218 8074 sales@coilcraft.com.cn  
**Singapore** + 65-6484 8412 sales@coilcraft.com.sg

Document 218-2 Revised 10/12/15

© Coilcraft Inc. 2017

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.