

Failure Rate Calculation

The steady-state FIT (Failure In Time) rate is calculated = $\lambda_G \pi_Q \pi_S \pi_T$ (failures/billion hours) per Telcordia Technologies Special Report SR-332, Issue 1, May 2001.

Where:

λ_G = chosen from Telcordia SR-332, Table 7-1 ($\geq 90\%$ upper confidence level)

π_Q = 1.0 (from from Telcordia SR-332, Table 7-4 for Quality Level II)

π_S = 1.0 (from from Telcordia SR-332, Table 7-6, assuming 50% electrical stress level)

π_T = 2.0 (calculated for +85°C per Table 7-7 with E_a activation energy = 0.15 eV)

RF Magnetics	Steady state FITs (failures/billion hours)	MTBF* (hours)
Chip inductors (all sizes)	1.0	1,000,000,000
Air core "Spring" inductors (all sizes)	1.0	1,000,000,000
90 Series axial lead inductors	1.0	1,000,000,000
RFID transponder coils	1.0	1,000,000,000
Tunable inductors (Unicoils, Slot Series)	2.0	500,000,000
Conical broadband inductors	38	26,315,789
Wideband RF transformers, chip transformers, baluns, directional couplers	60	16,666,667
Power Magnetics	Steady state FITs (failures/billion hours)	MTBF* (hours)
Power chip inductors (PS, FS – all sizes)	38	26,315,789
SMT inductors (DH, DO, DS, DT, EPL, LPD, LPO, LPS, ME, MLC, MOS, MSD, MSS, MVR, SER, SLC and XxL Series)	38	26,315,789
Coupled power inductors (LPD, MSD, PFD)	38	26,315,789
Fixed inductors (PCH, PCV, DMT, Mag Amps, etc.)	38	26,315,789
Transformers (including base/gate drive, power factor controller, planar and CCFL)	38	26,315,789
Current sensors	38	26,315,789
EMI Magnetics and LC Filters	Steady state FITs (failures/billion hours)	MTBF* (hours)
Filter coils (including PDLF, PTRF, CCDLF, TTDLF, DLF)	38	26,315,789
Common mode chokes (including DLF, PDLF, CCDLF, TTDLF, TRF, PTRF, TTTRF, P32xx, BU, USB Series)	38	26,315,789
Filtered connectors (including TRFRJ, PCRJ, DLC)	38	26,315,789
Filter assemblies (including PxLP and SxxP)	12	83,333,333
xDSL Magnetics	Steady state FITs (failures/billion hours)	MTBF* (hours)
xDSL transformers	38	26,315,789

*Calculated from FITs (MTBF=10⁹ (hours) / FITs)



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 292 Revised 06/12/14
 © Coilcraft Inc. 2014
 This product may not be used in medical or high
 risk applications without prior Coilcraft approval.
 Specification subject to change without notice.
 Please check web site for latest information.