


# Wideband Bias Chokes - 4310LC



- Flat bandwidth with high impedance to 6 GHz
- Low DCR and excellent current handling
- Ideal for use in high current bias Tee applications

**Core material** Ferrite

**Environmental** RoHS compliant, halogen free

**Terminations** RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.

**Weight** 0.42 g

**Ambient temperature** -40°C to +85°C with Irms current.

**Maximum part temperature** +125°C (ambient + temp rise)

**Storage temperature** Component: -40°C to +85°C.

Tape and reel packaging: -40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Failures in Time (FIT) / Mean Time Between Failures (MTBF)**

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

**Packaging** 350/7" reel, 1500/13" reel; Plastic tape: 24 mm wide, 0.3 mm thick, 12 mm pocket spacing, 3.5 mm pocket depth

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

Part number <sup>1</sup>	Inductance <sup>2</sup> ±10% (µH)	SRF (typ) <sup>3</sup> (MHz)	DCR (max) <sup>4</sup> (mOhm)	Irms (A) <sup>5</sup>	
				20°C rise	40°C rise
4310LC-132KE_	1.30	235	15.1	2.7	4.2
4310LC-352KE_	3.50	188	49.0	2.3	3.1

1. When ordering, please specify **packaging** code:

**4310LC-132KEC**

**Packaging:** C = 7" machine-ready reel. EIA-481 embossed plastic tape (350 parts per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter C instead.

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (1500 parts per full reel).

2. Inductance measured at 100 kHz, 0.1 Vrms, 0 Adc using an Agilent/HP 16193 fixture in Agilent/HP 4284A impedance analyzer. or equivalents.


3. SRF measured using Agilent/HP 8753D network analyzer or equivalent and a Coilcraft SMD-F test fixture.

4. DCR measured on Keithley 580 micro-ohmmeter or equivalent.

5. Current that causes the specified temperature rise from 25°C ambient. Because of their open construction, these parts will not saturate.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.




Dimensions are in  $\frac{\text{inches}}{\text{mm}}$




# Wideband Bias Chokes - 4310LC

## Insertion Loss (Ref: 50 Ohms)



## Impedance vs Frequency



Insertion loss measured in a bias tee configuration with an Agilent/HP 8753ES network analyzer.

