




# SMT Power Transformer

For Analog Devices ADM2482E and  
ADM2487E RS-485 Transceivers



- Designed specifically for use with Analog Devices ADM2482E and ADM2487E High Speed, Isolated RS-485 Transceivers with Integrated Transformer Driver
- Center tapped primary and secondary
- 2500 Vrms primary to secondary isolation

**Core material** Ferrite

**Terminations** RoHS compliant tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

**Weight** 1.0 g

**Ambient temperature** -40°C to +125°C

**Storage temperature** Component: -40°C to +125°C.

Tape and reel packaging: -40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Packaging** 600 per 13" reel; Plastic tape: 24 mm wide, 0.37 mm thick, 16 mm pocket spacing, 6.1 mm pocket depth

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

Part number <sup>1</sup>	Pri/sec voltage	Inductance <sup>2</sup> min (µH)	DCR max (Ohms) <sup>3</sup>		Leakage inductance <sup>4</sup> max (µH)	Volt-time product <sup>5</sup> (V-µsec)	Power <sup>6</sup> (W)	Turns ratio pri : sec
			1/2 pri	1/2 sec				
GA3157-AL_	5 V to 3.3 V	45.6	0.130	0.155	1.14	34.4	7.2	1 : 0.88

1. When ordering, please specify **termination** and **packaging** codes:


**GA3157-ALD**

**Termination:** L = RoHS compliant tin-silver over tin over nickel over phos bronze. **Special order:** T = RoHS tin-silver-copper (95.5/4/0.5) or S = non-RoHS tin-lead (63/37).

**Packaging:** D = 13" machine ready reel. EIA-481 embossed plastic tape (600 per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.

- Inductance is tested between pins 4 and 3 at 500 kHz, 0.5 Vrms, 0 Adc.
- DCR is for each half of the primary and secondary.
- Leakage inductance is for the primary with both windings connected in series and with the secondary windings shorted.
- Based on Bsat of the core at 25°C and number of turns on winding 4-3.
- Calculated output power based on 150 kHz operating frequency. Power varies depending on application.
- Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Primary windings and secondary windings to be connected in series on the PC board.

