

## Gate Drive Transformer For use with TI UCD3138 Digital Power Controllers

## **Digital Power Controllers**



- · Selected by Texas Instruments for their UCD3138 evaluation boards.
- Designed to meet UL/CSA/IEC 60950 Reinforced Insulation specification; 3.0 mm creepage and clearance.
- · Isolation: 3000 Vrms primaries to secondary; 500 Vrms windings to core

Core material Ferrite

Terminations RoHS compliant tin-silver over tin over nickel over phos-bronze.

Weight 6.3 g

Ambient temperature -40°C to +85°C

Maximum part temperature +125°C (ambient + temp rise) Storage temperature Component: -40°C to +125°C. Packaging: -40°C to +80°C

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 200/13" reel Plastic tape: 44 mm wide, 0.4 mm thick, 24 mm pocket spacing, 10.56 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787\_PCB\_Washing.pdf.

Part number <sup>1</sup>	Turns ratio	Primary inductance <sup>2</sup> ±25% (μΗ)	Leakage inductance <sup>3</sup> max (µH)	DCR max (Ohms)	Volt-time product⁴ (V-µsec)	SRF typ⁵ (MHz)	Capacitance max (pF)
GA3550-BL_	1:1:1	460	1.15 (Pri [A]) 1.25 (Pri [B])	0.410 (Pri [A]) 0.475 (Pri [B]) 0.440 (sec)	165	5.85	34.0 (1–10) 10.5 (1–5)

1. When ordering, please specify a packaging code:

GA3550-BLD Packaging: D = 13" machine ready reel. EIA-481 embossed plastic tape (200 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

B = Less than full reel. In an effort to simplify our part numbering system, Collcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D. 2. Inductance is for each winding, measured at 200 kHz, 0.4 Vrms, 0 Adc.

3. Leakage inductance is measured at 200 kHz, 0.4 Vrms with secondary

pins shorted.

Volt-time product is per winding.
SRF is per winding, measured on an Agilent/HP 4192 or equivalent.

Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



www.coilcraft.com

UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information