# **SMT** Power Transformers





- Optimized for Texas Instruments SN6501, ISO1176T/35T/3086T and Analog Devices ADM2482E/2485/2487E RS-485 Transceivers
- · Center tapped primary and secondary windings
- AEC-Q200 Grade 1 (-40°C to +125°C)
- 2500 Vrms, one minute interwinding isolation.
- Contact us for 8 mm creepage and clearance options.

### Core material Ferrite

Terminations RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 0.94 - 1.0 g

Ambient temperature -40°C to +125°C

Storage temperature Component: -40°C to +125°C.

Tape and reel packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C /

85% relative humidity) Packaging 600/13" reel Plastic tape: 24 mm wide, 0.37 mm thick,

16 mm pocket spacing, 6.1 mm pocket depth

PCB washing Tested with pure water or alcohol only. For other solvents, see Doc787\_PCB\_Washing.pdf

Part number <sup>1</sup>	Pri/sec voltage	Inductance <sup>2</sup> min (µH)	DCR ma pri	x (Ohms) <sup>3</sup> sec	Leakage inductance <sup>4</sup> max (µH)	Volt-time product⁵ (V-µsec)	Power <sup>6</sup> (W)	Turns ratio pri : sec
DA2303-AL_	5 V to 6 V	45.6	0.130	0.260	1.0	34.4	7.2	1:1.5
DA2304-AL_	3.3 V to 6 V	17.8	0.086	0.232	0.43	21.5	7.2	1:2.2

1. When ordering, please specify termination and packaging codes:

#### DA2303-ALD

Termination: L = RoHS compliant tin-silver over tin over nickel over phos bronze.

Special order:

T = RoHS tin-silver-copper (95.5/4/0.5) or

S = non-RoHS tin-lead (63/37).

- Packaging: D = 13" machine ready reel. EIA-481 embossed plastic tape (600 per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
  - $\mathbf{B}$  = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D
- 2. Inductance is tested between pins 4 and 3 at 500 kHz, 0.5 Vrms, 0 Adc.
- 3. DCR is per winding.
- 4. Leakage inductance is for the primary with both windings connected in series and with the secondary windings shorted.
- 5. Volt-time product is for the primary, between pins 4 and 1 with pins 2 and 3 connected.
- 6. Calculated output power based on 150 kHz operating frequency. Power varies depending on application.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



0.235 max

5.97



Primary windings and secondary windings to be connected in series on the PC board.



Parts manufactured prior





0.004/0,10



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

## Document 550 Revised 03/11/22

© Coilcraft Inc. 2022

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.