

# Shielded Power Inductors – LPS3314



- Very low DCR; excellent current handling
- Miniature 3.3 × 3.3 mm footprint; less than 1.4 mm tall

**Designer's Kit C330** contains 3 each of all values

**Core material** Ferrite

**Core and winding loss** See [www.coilcraft.com/coreloss](http://www.coilcraft.com/coreloss)

**Environmental** RoHS compliant, halogen free

**Terminations** RoHS compliant matte tin over nickel over silver.

Other terminations available at additional cost.

**Weight** 44.1 – 46.5 mg

**Ambient temperature** –40°C to +85°C with (40°C rise) Irms current.

**Maximum part temperature** +125°C (ambient + temp rise). [Derating](#).

**Storage temperature** Component: –40°C to +125°C.

Tape and reel packaging: –40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Failures in Time (FIT) / Mean Time Between Failures (MTBF)**

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

**Packaging** 1000/7" reel; 3500/13" reel Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 1.52 mm pocket depth

**Recommended pick and place nozzle** OD: 3.3 mm; ID: ≤ 1.65 mm

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (µH)	DCR max <sup>3</sup> (Ohms)	SRF typ <sup>4</sup> (MHz)	Isat (A) <sup>5</sup>			Irms (A) <sup>6</sup>	
				10% drop	20% drop	30% drop	20°C rise	40°C rise
LPS3314-102MR_	1.0	0.062	215	1.8	1.9	2.0	1.6	2.10
LPS3314-222MR_	2.2	0.100	140	1.3	1.4	1.5	1.2	1.60
LPS3314-332MR_	3.3	0.145	115	1.1	1.2	1.3	1.0	1.35
LPS3314-472MR_	4.7	0.175	86	0.97	0.99	1.0	0.90	1.25
LPS3314-562MR_	5.6	0.220	74	0.92	0.95	0.98	0.82	1.10
LPS3314-682MR_	6.8	0.240	72	0.87	0.90	0.91	0.82	1.10
LPS3314-822MR_	8.2	0.270	60	0.58	0.75	0.78	0.70	1.00
LPS3314-103MR_	10	0.330	55	0.56	0.66	0.70	0.65	0.87
LPS3314-153MR_	15	0.440	45	0.46	0.56	0.59	0.62	0.82
LPS3314-183MR_	18	0.575	37	0.44	0.51	0.54	0.52	0.68
LPS3314-223MR_	22	0.720	34	0.44	0.48	0.49	0.45	0.60
LPS3314-333MR_	33	0.920	27	0.30	0.38	0.40	0.43	0.58
LPS3314-473MR_	47	1.40	22	0.28	0.33	0.34	0.35	0.47
LPS3314-563MR_	56	1.55	19	0.26	0.30	0.31	0.32	0.42
LPS3314-683MR_	68	1.80	17	0.22	0.26	0.29	0.30	0.40
LPS3314-823MR_	82	2.00	14	0.20	0.24	0.26	0.29	0.39
LPS3314-104MR_	100	2.75	13	0.19	0.23	0.24	0.24	0.32
LPS3314-124MR_	120	3.45	11	0.19	0.21	0.22	0.22	0.30
LPS3314-154MR_	150	4.10	10	0.16	0.19	0.20	0.20	0.27
LPS3314-184MR_	180	4.80	9.0	0.14	0.17	0.18	0.19	0.25
LPS3314-224MR_	220	6.00	7.0	0.14	0.16	0.17	0.16	0.22
LPS3314-334MR_	330	9.30	6.0	0.11	0.12	0.13	0.13	0.18
LPS3314-474MR_	470	12.0	4.5	0.10	0.11	0.11	0.12	0.16
LPS3314-564MR_	560	14.0	4.5	0.095	0.105	0.11	0.11	0.145
LPS3314-684MR_	680	18.5	4.0	0.092	0.100	0.105	0.095	0.125
LPS3314-824MR_	820	24.0	3.7	0.086	0.099	0.100	0.085	0.110

1. Please, specify **termination** and **packaging** codes:

**LPS3314-824MR\_C**

**Termination:** R= RoHS compliant matte tin over nickel over silver.

Special order, added cost:

**Q** = RoHS tin-silver-copper (95.5/4/0.5)

or **P** = non-RoHS tin-lead (63/37).

**Packaging:** C= 7" machine-ready reel. EIA-481 embossed plastic tape (1000 parts per full reel).

**B**= Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter C instead.

**D**= 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (3500 parts per full reel).

2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc using an Agilent/HP 4192A impedance analyzer or equivalent. Inductance at 1 MHz is the same for parts with SRF ≥10 MHz.
3. DCR measured on a micro-ohmmeter.
4. SRF measured using Agilent/HP 8753ES or equivalent.
5. DC current at 25°C that causes the specified inductance drop from its value without current. [Click for temperature derating information.](#)
6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. [Click for temperature derating information.](#)
7. Electrical specifications at 25°C. Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



[www.coilcraft.com](http://www.coilcraft.com)

**US** +1-847-639-6400 [sales@coilcraft.com](mailto:sales@coilcraft.com)

**UK** +44-1236-730595 [sales@coilcraft-europe.com](mailto:sales@coilcraft-europe.com)

**Taiwan** +886-2-2264 3646 [sales@coilcraft.com.tw](mailto:sales@coilcraft.com.tw)

**China** +86-21-6218 8074 [sales@coilcraft.com.cn](mailto:sales@coilcraft.com.cn)

**Singapore** + 65-6484 8412 [sales@coilcraft.com.sg](mailto:sales@coilcraft.com.sg)

Document 541-1 Revised 03/31/17


© Coilcraft Inc. 2017

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.





# Shielded Power Inductors – LPS3314 Series

## Typical L vs Frequency



## Typical L vs Current



**Packaging** 1000/7" reel; 3500/13" reel Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 1.52 mm pocket depth

**NOTE NEW PART ORIENTATION** Parts are rotated 90° in the packaging tape compared to previous versions of this product.

