


Shielded Power Inductors XEL3520



- AEC-Q200 Grade 1 qualified
- Extremely low DCR and ultra low AC losses for high switching frequencies (2 to 5 MHz)
- Superior current handling with soft saturation characteristics
- Can withstand high current spike

Designer's Kit C465 contains 3 each of all values of the XEL3515, XEL3520 and XEL3530 series

Core material Composite

Environment RoHS compliant, halogen free

Terminations RoHS compliant, tin-silver over copper.

Weight 105 – 111 mg

Ambient temperature –40°C to +125°C with (40°C rise) Irms current.

Maximum part temperature +165°C (ambient + temp rise).

Storage temperature Component: –40°C to +165°C.

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Part number ¹	Inductance ² ±20% (µH)	DCR (mOhms) ³		SRF typ ⁴ (MHz)	Isat (A) ⁵			Irms (A) ⁶	
		typ	max		10% drop	20% drop	30% drop	20°C rise	40°C rise
XEL3520-700ME_	0.070	2.45	2.85	471	9.7	13.0	18.5	5.3	7.5
XEL3520-131ME_	0.13	3.50	4.05	294	7.2	9.8	13.8	4.5	6.4
XEL3520-201ME_	0.20	4.90	5.65	227	5.7	8.6	11.8	4.0	5.6
XEL3520-331ME_	0.33	8.00	9.20	158	3.9	6.2	8.7	3.2	5.0
XEL3520-471ME_	0.47	9.44	10.85	135	3.7	5.7	8.0	2.9	4.6
XEL3520-561ME_	0.56	14.50	16.70	129	3.3	5.4	7.3	2.4	3.8
XEL3520-801ME_	0.80	20.50	23.55	94	2.5	4.0	5.6	2.0	3.1
XEL3520-112ME_	1.1	31.50	36.25	80	2.2	3.5	5.0	1.7	2.7
XEL3520-122ME_	1.2	35.00	40.25	70	2.0	3.2	4.8	1.5	2.5

1. When ordering, please specify **packaging** code:

XEL3520-112MEC

Packaging: **C** = 7" machine-ready reel. EIA-481 embossed plastic tape (1000 parts per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter C instead.

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (3000 parts per full reel).

2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using Agilent/HP 4395A or equivalent.

5. DC current at 25°C that causes the specified inductance drop from its value without current.

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing

Irms testing was performed on 0.75 inch wide × 0.25 inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.



www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com

UK +44-1236-730595 sales@coilcraft-europe.com

Taiwan +886-2-2264 3646 sales@coilcraft.com.tw

China +86-21-6218 8074 sales@coilcraft.com.cn

Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1340-1 Revised 04/07/17










© Coilcraft Inc. 2017

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

NEW!

Shielded Power Inductors – XEL3520

L vs Current






US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1340-2 Revised 04/07/17
 © Coilcraft Inc. 2017
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.


NEW!

Shielded Power Inductors – XEL3520

L vs Frequency




Recommended Land Pattern



Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Packaging 1000/7" reel; 3000/13" reel
Plastic tape: 12 mm wide, 0.21 mm thick,
8 mm pocket spacing, 2.2 mm pocket depth



Part orientation in tape

