




Shielded Power Inductors – XGL1313



- Industry's lowest DCR and low power losses
- Wide inductance range up to 47 μH
- High current handling with soft saturation characteristics
- AEC-Q200 qualified with a 165°C max part temperature

Designer's Kit C518 contains 3 of each value

Core material Composite

Core and winding loss See www.coilcraft.com/coreloss

Environmental RoHS compliant, halogen free

Terminations RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.

Weight 13 – 16 g

Operating voltage: 60 V⁷

Ambient temperature –40°C to +125°C with (40°C rise) Irms current.

Maximum part temperature +165°C (ambient + temp rise). [Derating](#).

Storage temperature Component: –55°C to +165°C.

Tape and reel packaging: –55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Inductance ² ±20% (μH)	DCR (mOhms) ³		SRF typ ⁴ (MHz)	Isat (A) ⁵			Irms (A) ⁶	
		typ	max		10% drop	20% drop	30% drop	20°C rise	40°C rise
XGL1313-152MED	1.5	1.0	1.2	30	24.5	39.0	53.0	35.4	48.7
XGL1313-222MED	2.2	1.4	1.6	25	21.0	33.5	46.0	32.9	45.1
XGL1313-332MED	3.3	2.0	2.3	20	18.0	29.0	40.0	28.9	39.7
XGL1313-472MED	4.7	2.5	2.8	16	16.0	25.0	35.0	26.7	36.7
XGL1313-682MED	6.8	3.8	4.3	13	12.5	19.5	26.5	22.5	31.0
XGL1313-822MED	8.2	4.4	5.2	12	11.3	18.2	25.0	20.9	28.7
XGL1313-103MED	10	5.5	6.3	10	10.5	17.0	23.0	19.0	26.0
XGL1313-153MED	15	8.0	9.2	8.1	8.1	13.0	17.5	15.5	21.3
XGL1313-223MED	22	11.6	13.3	7.1	7.3	11.5	15.4	12.6	17.2
XGL1313-333MED	33	18.3	20.7	5.8	5.6	8.5	11.6	9.3	12.6
XGL1313-473MED	47	26.5	30.0	5.0	4.7	7.3	9.7	7.1	9.1

1. When ordering, please specify **termination** code:

XGL1313-473MED

Termination: E = RoHS compliant tin-silver over copper.

Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or S = non-RoHS tin-lead (63/37).

Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (200 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.

3. DCR measured on a micro-ohmmeter.

4. SRF measured using Agilent/HP 4395A or equivalent.

5. DC current at 25°C that causes an inductance drop from its value without current.

6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. Temperature rise is highly dependent on many factors including pcb land pattern, trace size, air flow, and proximity to other components. Therefore temperature rise should be verified in application conditions. [Click for temperature derating information](#).

7. Voltage capability varies by part number and in many cases may be higher than the listed voltage.

8. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com

UK +44-1236-730595 sales@coilcraft-europe.com

Taiwan +886-2-2264 3646 sales@coilcraft.com.tw

China +86-21-6218 8074 sales@coilcraft.com.cn

Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1730-1 Revised 02/19/26











© Coilcraft Inc. 2026

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



Shielded Power Inductors – XGL1313

Typical L vs Current





US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1730-2 Revised 02/19/26
 © Coilcraft Inc. 2026
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.






Shielded Power Inductors – XGL1313

Typical L vs Current




Dash number indicates direction of terminals and start (short) lead. Connect high dv/dt here for lowest EMI.

Typical L vs Frequency



Recommended Land Pattern



* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0,13 mm

Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Packaging 200/13" reel Plastic tape: 32 mm wide, 0.50 mm thick, 24 mm pocket spacing, 13.2 mm pocket depth



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1730-3 Revised 02/19/26
 © Coilcraft Inc. 2026
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.