

Shielded Power Inductors – LPS4414

Improved version now available.

These parts are not recommended for new designs. They are replaced by new lead free and halogen free versions which are identical in form, fit and function. See www.coilcraft.com/lps4414.cfm.



- Very low DCR; excellent current handling
- 4.4 × 4.4 mm footprint; only 1.4 mm tall

Core material Ferrite

Core and winding loss See www.coilcraft.com/coreloss

Terminations RoHS compliant silver-palladium-platinum-glass frit. Other terminations available at additional cost.

Weight 82.3 – 89.8 mg

Ambient temperature –40°C to +85°C with (40°C rise) Irms current.

Maximum part temperature +125°C (ambient + temp rise). **Derating.**

Storage temperature Component: –40°C to +125°C.

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 1000/7" reel; 3500/13" reel Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 1.52 mm pocket depth (Refer to dimensional drawing for part orientation in tape.)

Recommended pick and place nozzle: OD: 4.5 mm; ID: ≤2 mm

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Inductance ² ±20% (μH)	DCR max ³ (Ohms)	SRF typ ⁴ (MHz)	Isat (A) ⁵			Irms (A) ⁶	
				10% drop	20% drop	30% drop	20°C rise	40°C rise
LPS4414-301ML	0.30	0.040	470	5.6	5.7	5.8	2.35	3.25
LPS4414-501ML	0.50	0.050	330	4.3	4.4	4.5	2.10	2.80
LPS4414-701ML	This part number has been changed to LPS4414-801.							
LPS4414-801ML	0.80	0.055	225	3.7	3.75	3.8	1.85	2.50
LPS4414-102ML	1.0	0.060	190	3.0	3.1	3.2	1.75	2.30
LPS4414-152ML	1.5	0.078	150	2.9	3.1	3.2	1.55	2.00
LPS4414-182ML	1.8	0.087	130	2.7	2.8	2.9	1.50	1.90
LPS4414-222ML	2.2	0.110	115	2.2	2.3	2.35	1.25	1.60
LPS4414-332ML	3.3	0.165	85.0	1.8	1.9	1.95	1.15	1.50
LPS4414-472ML	4.7	0.215	68.0	1.4	1.5	1.55	0.90	1.20
LPS4414-562ML	5.6	0.260	58.0	1.4	1.4	1.5	0.75	1.10
LPS4414-682ML	6.8	0.270	54.0	1.2	1.3	1.4	0.70	1.00
LPS4414-822ML	8.2	0.350	50.0	1.1	1.3	1.3	0.70	0.98
LPS4414-103ML	10	0.380	43.0	1.1	1.2	1.3	0.70	0.95
LPS4414-123ML	12	0.380	38.0	0.94	0.97	1.0	0.66	0.88
LPS4414-153ML	15	0.440	36.0	0.85	0.89	0.92	0.63	0.82
LPS4414-183ML	18	0.530	31.0	0.76	0.80	0.82	0.56	0.75
LPS4414-223ML	22	0.590	27.0	0.69	0.72	0.74	0.53	0.68
LPS4414-333ML	33	0.715	23.0	0.47	0.49	0.51	0.49	0.65
LPS4414-473ML	47	0.935	18.0	0.39	0.42	0.43	0.44	0.58
LPS4414-563ML	56	1.15	16.0	0.37	0.39	0.40	0.42	0.54
LPS4414-683ML	68	1.35	14.6	0.32	0.33	0.34	0.36	0.48
LPS4414-104ML	100	1.90	11.0	0.26	0.28	0.285	0.31	0.40
LPS4414-124ML	120	2.60	10.0	0.23	0.24	0.25	0.27	0.34
LPS4414-154ML	150	3.10	9.0	0.22	0.23	0.24	0.24	0.32
LPS4414-224ML	220	4.10	6.7	0.18	0.20	0.20	0.22	0.29
LPS4414-334ML	330	6.00	5.6	0.14	0.16	0.165	0.17	0.23
LPS4414-474ML	470	9.50	4.3	0.13	0.14	0.145	0.14	0.23
LPS4414-564ML	560	10.7	4.0	0.12	0.13	0.14	0.13	0.17
LPS4414-684ML	680	11.7	3.5	0.10	0.11	0.12	0.13	0.17
LPS4414-824ML	820	15.1	3.0	0.10	0.105	0.11	0.11	0.14
LPS4414-105ML	1000	16.3	2.6	0.10	0.102	0.106	0.10	0.13
LPS4414-155ML	1500	26.4	2.2	0.096	0.099	0.100	0.085	0.11
LPS4414-185ML	1800	35.0	1.9	0.089	0.094	0.097	0.075	0.10
LPS4414-225ML	2200	42.5	1.9	0.082	0.089	0.092	0.065	0.080
LPS4414-335ML	3300	56.0	1.3	0.072	0.078	0.083	0.055	0.070

1. Please specify **termination** and **packaging** codes:

LPS4414-223MLC

Termination: L = RoHS compliant silver-palladium-platinum-glass frit.
Special order:

T = RoHS tin-silver-copper (95.5/4/0.5)
or S = non-RoHS tin-lead (63/37).

Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (1000 parts per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter C instead.

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (3500 parts per full reel).

- Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.
- DCR measured on a micro-ohmmeter.
- SRF measured using Agilent/HP 8753ES or equivalent.
- DC current at which the inductance drops the specified amount from its value without current. [Click for temperature derating information.](#)
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. [Click for temperature derating information.](#)
- Electrical specifications at 25°C. Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Coilcraft[®]

www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com

UK +44-1236-730595 sales@coilcraft-europe.com

Taiwan +886-2-2264 3646 sales@coilcraft.com.tw

China +86-21-6218 8074 sales@coilcraft.com.cn

Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 548NR-1 Revised 04/14/18


© Coilcraft Inc. 2018

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.





Shielded Power Inductors – LPS4414 Series

Typical L vs Current



Typical L vs Frequency



Packaging 1000/7" reel; 3500/13" reel Plastic tape: 12 mm wide, 0.3 mm thick, 8 mm pocket spacing, 1.52 mm pocket depth

Orientation of parts in packaging tape

