


NEW!

Flyback Transformer ZD2024-AE



- Optimized for iso-buck converters for more efficient power supplies
- Designed to operate up to 500 kHz with 5 – 12 V input
- 2000 Vrms, one minute isolation (hipot) between primary and secondary
- Lower profile than other core/bobbin sets
- AEC-Q200 qualified


Core material Ferrite**Environment** RoHS compliant, halogen free**Terminations** Tin-silver-copper over tin over nickel over phos bronze**Weight** 5.43 – 5.63 g**Ambient temperature** –40°C to +125°C**Maximum part temperature** +165°C (Ambient + temp rise)**Storage temperature** Component: –40°C to +125°C

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles**Packaging** 200/13" reel Plastic tape: 44 mm wide, 0.4 mm thick, 28 mm pocket spacing, 9.3 mm pocket depth**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)


Part number ¹	L at 0 A ² ±10% (μH)	DCR max (Ohms)					Leakage L ³ max (μH)	Turns ratio					Isolation ⁴ (Vrms)	Isat ⁵ (A)	Output
		pri	sec1	sec2	sec3	sec4		pri	sec1	sec2	sec3	sec4			
ZD2024-AED	40	0.135	1.95	1.95	1.95	2.4	0.32	1	: 2.5	: 2.5	: 2.5	: 2.5	2000	3.8	12 V, 0.25 A

- Packaging:** D = 13" machine-ready reel. EIA-481 embossed plastic tape (200 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - Inductance is for the primary, measured at 500 kHz, 0.1 Vrms, 0 Adc.
 - Leakage inductance is for the primary with the secondary windings shorted.
 - 2000 Vrms, one minute isolation (hipot) between primary and secondary windings.
 - DC current that causes the primary inductance to drop 30% from its value without current.
 - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.








Flyback Transformer for ZD2024-AE



L vs Current



Dimensions are in $\frac{\text{inches}}{\text{mm}}$



www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1802-2 Revised 03/29/24

© Coilcraft Inc. 2025

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.