


VERY LOW AC AND DC LOSSES

High Voltage Shielded Power Inductor XEL4030V



- Extremely low DCR and ultra low AC losses for high switching frequencies (2 to 5 MHz)
- High-voltage rating of 120 V—50% higher than the standard series. Learn more about [Voltage Ratings for Inductors](#)
- AEC-Q200 Grade 1 (-40°C to +125°C)
- Superior current handling with soft saturation characteristics
- Can withstand high current spikes
- Designed for high temperature applications

Core material Composite

Environment RoHS compliant, halogen free

Terminations RoHS compliant, tin-silver over copper.

Weight 0.28 g

Operating voltage: 0 – 120 V

Ambient temperature -40°C to +125°C with (40°C) Irms current.

Maximum part temperature +165°C (ambient + temp rise).

Storage temperature Component: -55°C to +165°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

0.48 per billion hours / 2.08E+09 hours, calculated per Telcordia SR-332

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787 PCB Washing.pdf](#).

| Part number ¹ | Inductance ² ±20% (µH) | DCR (mOhms) ³ | | SRF typ ⁴ (MHz) | Isat ⁵ (A) | Irms (A) ⁶ | |
|--------------------------|--------------------------------------|--------------------------|------|-------------------------------|--------------------------|-----------------------|-----------|
| | | typ | max | | | 20°C rise | 40°C rise |
| XEL4030V-101ME_ | 0.10 | 1.50 | 1.80 | 240 | 30.0 | 20.4 | 25.8 |
| XEL4030V-201ME_ | 0.20 | 2.15 | 2.40 | 155 | 22.0 | 17.0 | 21.6 |
| XEL4030V-301ME_ | 0.30 | 2.80 | 3.10 | 115 | 19.0 | 14.9 | 18.9 |
| XEL4030V-471ME_ | 0.47 | 4.10 | 4.60 | 95 | 15.5 | 12.3 | 15.6 |
| XEL4030V-641ME_ | 0.64 | 5.30 | 5.90 | 80 | 13.5 | 10.9 | 13.7 |
| XEL4030V-901ME_ | 0.90 | 8.00 | 8.80 | 68 | 10.0 | 8.8 | 11.2 |
| XEL4030V-102ME_ | 1.0 | 8.89 | 9.78 | 65 | 9.0 | 8.4 | 10.7 |
| XEL4030V-122ME_ | 1.2 | 10.4 | 11.5 | 60 | 8.7 | 7.8 | 9.8 |
| XEL4030V-152ME_ | 1.5 | 15.1 | 16.6 | 58 | 8.5 | 6.4 | 8.1 |
| XEL4030V-222ME_ | 2.2 | 20.1 | 22.1 | 40 | 6.1 | 5.8 | 7.8 |
| XEL4030V-332ME_ | 3.3 | 26.1 | 28.6 | 35 | 5.9 | 5.0 | 6.6 |
| XEL4030V-472ME_ | 4.7 | 40.0 | 44.1 | 30 | 4.6 | 3.9 | 5.1 |
| XEL4030V-682ME_ | 6.8 | 67.4 | 74.1 | 20 | 3.6 | 3.0 | 3.9 |

Irms Testing

Irms testing was performed on 0.75 inch wide x 0.25 inch thick copper traces in still air. Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.

1. When ordering, please specify **packaging** code:

XEL4030V-682MEC

Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (500 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (2000 parts per full reel).

- Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.
- DCR measured on a micro-ohmmeter.
- SRF measured using Agilent/HP 4395A or equivalent.
- DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- Electrical specifications at 25°C.











Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

**VERY LOW AC
AND DC LOSSES**



High Voltage Shielded Power Inductor – XEL4030V

L vs Current






US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1526-2 Revised 04/13/21
 © Coilcraft Inc. 2021
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



VERY LOW AC AND DC LOSSES

High Voltage Shielded Power Inductor – XEL4030V




L vs Current



Typical L vs Frequency



Dash number indicates direction of terminals and start (short) lead. Connect high dv/dt here for lowest EMI.



Recommended Land Pattern

Dimensions are in inches / mm

| Dash number | Height* max (in / mm) |
|-------------|-----------------------|
| -101 | 0.126 / 3.20 |
| -201 | 0.126 / 3.20 |
| -301 | 0.126 / 3.20 |
| -471 | 0.122 / 3.10 |
| -641 | 0.122 / 3.10 |
| -911 | 0.122 / 3.10 |
| -102 | 0.122 / 3.10 |
| -122 | 0.122 / 3.10 |
| -152 | 0.122 / 3.10 |
| -222 | 0.122 / 3.10 |
| -332 | 0.122 / 3.10 |
| -472 | 0.122 / 3.10 |
| -682 | 0.122 / 3.10 |

* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0.13 mm.

Packaging 500/7" reel; 2000/13" reel Plastic tape: 12 mm wide, 0.23 mm thick, 8 mm pocket spacing, 3.25 mm pocket depth



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1526-3 Revised 04/13/21

© Coilcraft Inc. 2021

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.