


Flyback Transformers

For Akros AS1135 **PoE Controller**



- Flyback transformers for IEEE802.3at PoE applications
- Input voltage GA3568: 36 57 V; HA3809: 10 57 V
- 1500 Vrms, one minute isolation from primary and bias to secondary and sync windings.

Core material Ferrite

Terminations RoHS tin-silver (96.5/3.5) over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 11.4 - 11.8 g

Ambient temperature -40°C to +125°C

Storage temperature Component: -40°C to +125°C. Tape and reel packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 175 per 13" reel Plastic tape: 44 mm wide, 0.4 mm thick, 32 mm pocket spacing, 11.9 mm pocket depth


PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.

Part	Inductance Inductance at 0 A ² at Ipk ³			DCR max (Ohms) ⁴			Leakage inductance ⁵	1	furns ratios ⁶		Ipk ³	
number ¹	±10%(µH)	min (µH)	pri	sec	bias	sync	max (µH)	pri:sec	pri:bias	pri:sync	(A)	Output ⁷
GA3568-DL_	60	54	0.132	0.0055	0.220	0.200	1.20	1:0.167	1:0.29	1:0.29	2.6	3.3 V, 9.1 A
HA3809-AL_	30	25	0.042	0.010	0.165	0.165	0.680	1:0.176	1:0.29	1:0.29	3.9	3.3 V, 9.1 A

1. When ordering, please specify termination and packaging codes:


HA3809-ALD

- Termination: L = RoHS tin-silver (96.5/3.5) over tin over nickel over phos bronze. Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).
- D = 13" machine-ready reel. EIA-481 embossed plastic tape (175 parts per full reel). Packaging: Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.
- 2. Inductance is for the primary, measured at 300 kHz, 0.7 Vrms. For the GA3568-DL inductance is per winding. 3. Peak primary current drawn at minimum input voltage.
- 4. DCR for the secondary is with the windings connected in parallel. For GA3568-DL DCR for the primary is with both windings connected in parallel.
- 5. Leakage inductance is for the primary windings with the secondary windings shorted.
- 6. Turns ratios are for the primary (windings connected in parallel for the GA3568-DL) and with the sec-
- ondary windings connected in parallel. Output of the secondary is with the windings connected in parallel. Bias winding output is 5 V, 20 mA. 7 Electrical specifications at 25°C
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Primary windings and secondary windings each to be connected in parallel on PC board.





connected in parallel on PC board


> US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

0.930


23.62

0.130

3 30



Parts manufactured prior to December 2011 may be marked differently.



Document 853 Revised 05/18/10

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

[©] Coilcraft Inc. 2021