

- Industry's lowest DCR and low power losses
- Wide inductance range up to 56 uH
- · High current handling with soft saturation characteristics
- AEC-Q200 Grade 1 (-40°C to +125°C) with a 165°C max part temperature

Designer's Kit C516 contains 3 of each value

Core material Composite

Core and winding loss See www.coilcraft.com/coreloss

Environmental RoHS compliant, halogen free

Terminations RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.

Weight 6.0 - 6.9 g

Operating voltage: 0 - 60 V

Ambient temperature -40°C to +125°C with (40°C rise) Irms current. Maximum part temperature +165°C (ambient + temp rise). Derating.

Storage temperature Component: -55°C to +165°C.

Tape and reel packaging: -55°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787\_PCB\_Washing.pdf.

	Inductance <sup>2</sup>	DCR (mOhms)3		SRF typ <sup>4</sup>	Isat (A) <sup>5</sup>			Irms (A) <sup>6</sup>	
Part number <sup>1</sup>	±20% (μH)	typ	max	(MHz)	10% drop	20% drop	30% drop	20°C rise	40°C rise
XGL1010-271MED	0.27	0.47	0.57	96	44	74	117	40.8	54.0
XGL1010-521MED	0.52	0.68	0.80	56	33	54	76	39.8	52.0
XGL1010-801MED	0.80	0.88	1.1	47	29	46	64	36.0	48.0
XGL1010-122MED	1.2	1.2	1.4	37	24	39	50	31.5	41.5
XGL1010-152MED	1.5	1.5	1.7	31	21	33	45	31.1	40.7
XGL1010-222MED	2.2	2.3	2.6	25	15	26	36	24.6	33.0
XGL1010-332MED	3.3	3.2	3.7	21	14	24	34	19.2	26.0
XGL1010-472MED	4.7	4.0	4.6	18	12	21	29	18.0	24.7
XGL1010-562MED	5.6	5.2	5.9	16	10	17	24	17.5	24.0
XGL1010-682MED	6.8	6.2	7.0	14	9.3	16	22	15.7	21.2
XGL1010-822MED	8.2	8.0	9.0	13	8.7	14	20	14.1	18.7
XGL1010-103MED	10	8.7	9.7	12	8.3	13	18	13.7	18.2
XGL1010-153MED	15	13.6	15.2	10	7.0	11	16	11.4	15.4
XGL1010-223MED	22	19.6	22.0	8.0	5.6	9.3	13	9.8	13.2
XGL1010-333MED	33	29.9	33.5	6.6	4.6	7.6	10	6.1	8.5
XGL1010-473MED	47	40.9	46.9	4.9	3.7	6.1	8.4	5.1	7.0
XGL1010-563MED	56	49.9	55.9	4.6	3.3	5.3	7.6	4.6	6.3

1. When ordering, please specify termination code:

#### XGL1010-563MED

**Termination: E** = RoHS compliant tin-silver over copper.

Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or S = non-RoHS tin-lead (63/37).

Packaging: D= 13" machine-ready reel. EIA-481 embossed plastic tape (300 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

- 2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop from its value without current.
- 6. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. Click for temperature derating information.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

## **Irms Testing**

Irms testing was performed on 0.75 inch wide × 0.25 inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw **China** +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg Document 1707-1 Revised 08/24/22

© Coilcraft Inc. 2022

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice.
Please check web site for latest information.




## Shielded Power Inductors - XGL1010





# **Typical L vs Current**





































## Shielded Power Inductors - XGL1010





#### Typical L vs Current





























## Shielded Power Inductors - XGL1010


#### Typical L vs Frequency











Packaging 300/13" reel Plastic tape: 24 mm wide, 0.4 mm thick, 16 mm pocket spacing, 10.21 mm pocket depth

