








Shielded Power Inductors – XAL1030



- · Very high current and low DCR
- Low profile, only 3 mm high
- Soft saturation makes them ideal for VRM/VRD applications.

Core material Composite

Environmental RoHS compliant, halogen free Terminations RoHS compliant tin-silver over copper. Other terminations available at additional cost. Weight 1.6 – 1.8 g Operating voltage: 0-60 V Ambient temperature -40°C to +125°C with (40°C rise) Irms current. Maximum part temperature +165°C (ambient + temp rise). Derating. Storage temperature Component: -55°C to +165°C. Tape and reel packaging: -55°C to +80°C Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity) Packaging 250/7" reel; 1000/13" reel Plastic tape: 24 mm wide, 0.3 mm thick, 16 mm pocket spacing, 3.25 mm pocket depth PCB washing Tested to MIL-STD-202 Method 215 plus an additional

aqueous wash. See Doc787_PCB_Washing.pdf.

	Inductance ²	DCR (mOhms) ³		SRF typ⁴	Isat	Irms (A) ⁶	
Part number ¹	±20% (μH)	typ	max	(MHz)	(A) ⁵	20°C rise	40°C rise
XAL1030-161ME_	0.16	1.10	1.21	120	88.0	28.0	42.0
XAL1030-301ME_	0.30	1.55	1.70	78	68.0	25.5	35.0
XAL1030-561ME_	0.56	2.50	2.75	53	44.0	23.0	32.0
XAL1030-102ME_	1.0	4.50	4.95	41	35.0	16.0	23.0

1. When ordering, please specify termination and packaging coded:

XAL1030-102MÉC

- **Termination: E** = RoHS compliant tin-silver over copper.
- **Special order: T** = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37). **Packaging: C** = 7'' machine-ready reel. EIA-481 embossed plastic tape (250 parts per full reel).
 - Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.
 - D = 13" machine-ready reel. EIA-481 embossed plastic tape (1000 parts per full reel). Factory order only, not stocked.
- 2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current. Click for temperature derating information.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. Click for temperature derating information.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



 US
 +1-847-639-6400
 sales@coilcraft.com

 UK
 +44-1236-730595
 sales@coilcraft-europe.com

 Taiwan
 +886-2-2264
 3646
 sales@coilcraft.com.tw

 China
 +86-21-6218
 8074
 sales@coilcraft.com.cn

 Singapore
 + 65-6484
 8412
 sales@coilcraft.com.sg

Document 962-1 Revised 06/21/21

© Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information


Irms Testing

Irms testing was performed on 0.75 inch wide $\times 0.25$ inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.




Shielded Power Inductors – XAL1030



L vs Frequency 10 Inductance (µH) 1.0 uH 0.56 µH 0.30 µH 0.16 µH 0.1 0.1 1 10 100 Frequency (MHz)

0.394 ±0.020 10,0 ±0,50 0.445 ±0.020 11,3 ±0,50



0.354 9,0

3,1



0.262

6,65

 $\frac{0.094}{2,38}$

Recommended Land Pattern

* For optional tin-lead and tin-silvercopper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.005 inch / 0.13 mm.

0.315 typ

8,0

Dimensions are in inches



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 962-2 Revised 06/21/21

© Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information