







Shielded Power Inductors-MLC1770





- Soft saturation makes them ideal for VRD/VRM applications
- Special materials eliminate all thermal aging issues.
- Saturation current up to 64 Amps

	Inductance ²	DCR (mOhm)		SRF typ ³	Isat (A) ⁴			Irms (A)⁵	
Part number ¹	±20% (μH)	typ	max	(MHz)	10% drop	20% drop	30% drop	20°C rise	40°C rise
MLC1770-801ME_	0.80	1.15	1.30	72	28.40	49.92	64.88	20.36	28.92
MLC1770-142ME_	1.40	1.80	2.00	59	20.52	35.64	51.44	16.10	24.06
MLC1770-202ME_	2.00	2.70	3.00	49	14.20	24.80	37.00	12.98	19.12
MLC1770-282ME_	2.80	3.60	4.00	41	13.00	22.80	33.80	11.56	15.80

1. When ordering, please specify $\ensuremath{\textit{termination}}$ and $\ensuremath{\textit{packaging}}$ codes:

MLC1770-282MEC

Termination	: E = RoHS compliant tin-silver over copper
	Special order, added cost: T = RoHS tin-silver-
	copper (95.5/4/0.5) or
	S = non-RoHS tin-lead (63/37).
Packaging:	$\mathbf{D} = 13''$ machine-ready reel. FIA-481 embossed plas

- Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (400 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.
- Inductance measured at 100 kHz, 0.1 Vrms, 0 Adc using a Coilcraft SMD-A fixture in an Agilent/HP 4263B LCR meter.
- 3. SRF measured using an Agilent/HP4291A impedance analyzer and an Agilent/HP 16193 fixture.
- 4. DC current at 25°C that causes the specified inductance drop from its value without current. Click for temperature derating information.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. Click for temperature derating information.

5. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Core material Iron

Core and winding loss Go to core loss calculator Environmental RoHS compliant, halogen free

Weight 7.8 – 8.0 g

Terminations RoHS compliant tin-silver (96.5/3.5) over copper. Other terminations available at additional cost.

Ambient temperature -40°C to +85°C with Irms current

Maximum part temperature: The part may be operated without damage as long its temperature (ambient + self-heating) does not exceed +125°C.

Storage temperature Component: -40° C to $+125^{\circ}$ C. Tape and reel packaging: -40° C to $+80^{\circ}$ C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at $<30^{\circ}C$ / 85% relative humidity)

Packaging 400 per 13" reel Plastic tape: 24 mm wide, 0.4 mm thick, 24 mm pocket spacing, 7.0 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg


Document 961-1 Revised 06/06/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.




Shielded Power Inductors – MLC1770

L vs Current




Current (A)



Dimensions are in $\frac{inches}{mm}$





Coilcraft www.coilcraft.com

 US
 +1-847-639-6400
 sales@coilcraft.com

 UK
 +44-1236-730595
 sales@coilcraft-europe.com

 Taiwan
 +886-2-2264
 3646
 sales@coilcraft.com.tw

 China
 +886-21-6218
 8074
 sales@coilcraft.com.cn

 Singapore
 + 65-6484
 8412
 sales@coilcraft.com.sg

Land Pattern

Document 961-2 Revised 06/06/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.