

## Coupled Inductors – LPR4012 For Step-Up, Resonant & Flyback Applications





- Miniature, shielded coupled inductors are only 1,1 mm high and 4 mm square
- Excellent coupling coefficient (k = 0.95) makes them ideal for use as flyback transformers in DC-DC converters or as coupled inductors in buck regulators to provide multiple outputs
- 100 Vrms, one minute isolation (hipot) between windings
- · Wide selection of turns ratios makes them suitable for a variety of voltage step-up and step-down applications
- Can also be used in autotransformer applications.
- · High Isat and low DCR ratings of these low profile parts provide high efficiency and excellent current handling in a rugged, low cost design
- · Custom inductance values and turn ratios are available upon request.

	Primary (L1) inductance <sup>2</sup> Turns		DCR max (Ohms)		SRF tvp <sup>3</sup>	Isat (A) <sup>4</sup>			Irms (A)⁵	
Part number <sup>1</sup>	± 20% (μH)	ratio	L1	L2	(MHz)	10% drop	20% drop	30% drop	20°C rise	40°C rise
LPR4012-202AMR_	2.0	1:1.5	0.240	0.325	61.5	1.70	1.73	1.74	1.10	1.45
LPR4012-202BMR_	2.0	1:2	0.240	0.480	49.4	1.70	1.73	1.74	1.10	1.45
LPR4012-202DMR_	2.0	1:3	0.240	1.15	31.0	1.70	1.73	1.74	1.10	1.45
LPR4012-202LMR_	2.0	1:10	0.240	11.62	7.43	1.70	1.73	1.74	1.10	1.45
LPR4012-103BMR_	10.0	1:2	0.600	1.55	19.5	0.62	0.64	0.65	0.52	0.70
LPR4012-103DMR_	10.0	1:3	0.600	3.71	12.8	0.62	0.64	0.65	0.52	0.70
LPR4012-223BMR_	22.0	1:2	1.16	3.65	11.2	0.43	0.45	0.46	0.43	0.57
LPR4012-223DMR_	22.0	1:3	1.16	7.08	8.00	0.43	0.45	0.46	0.43	0.57

1. When ordering, please specify termination and packaging codes:

LPR4012-223XMRC

Termination: R = RoHS compliant matte tin over nickel over silver.

Special order:  $\mathbf{Q} = \text{RoHS}$  tin-silver-copper (95.5/4/0.5) or  $\mathbf{P} = \text{non-RoHS}$  tin-lead (63/37).

Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (1000 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (3500 parts per full reel).

B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.

2. Inductance is measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent.

3. SRF measured using an Agilent/HP 4191A or equivalent. When leads are connected in parallel, SRF is the same value.

4. DC current at 25°C applied to L1 that causes the specified inductance drop from its value without current.

5. Current applied to L1 that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

## Document 713-1 Revised 12/13/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



## **Coupled Inductors – LPR4012 Series**



Typical Buck Converter with auxiliary output



## **Typical Flyback Converter**



For optional tin-lead and tin-silver-copper mounted part. Dimensions before mounting can be an additional 0.005 inch / 0,13 mm).



inches Dimensions are in mm



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg Document 713-2 Revised 12/13/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

Core material Ferrite

Weight 54 - 64 mg

Terminations RoHS compliant matte tin over nickel over silver. Other terminations available at additional cost.

Ambient temperature -40°C to +85°C with Irms current

Maximum part temperature +125°C (ambient + temp rise)

Storage temperature Component: -40°C to +125°C. Tape and reel packaging: -40°C to +80°C

Winding to winding isolation 100 Vrms

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 1000/7" reel; 3500/13" reel Plastic tape: 12 mm wide, 0.25 mm thick, 8 mm pocket spacing, 1.45 mm pocket depth Recommended pick and place nozzle OD: 4 mm; ID: ≤ 2 mm

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787\_PCB\_Washing.pdf.