



**HIGH ISOLATION**

# Coupled Inductors – MSD1038V






- High isolation voltage, 2250 Vrms, one minute isolation (hipot) between primary and secondary windings
- Ideal for use in a variety of circuits including flyback, multi-output buck, SEPIC, Cuk and Zeta.
- High efficiency and excellent current handling
- Provides Functional Insulation
- AEC-Q200 qualified



\* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.012 inch (0.3 mm).

Dimensions are in inches/mm



www.coilcraft.com

**US** +1-847-639-6400 sales@coilcraft.com  
**UK** +44-1236-730595 sales@coilcraft-europe.com  
**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw  
**China** +86-21-6218 8074 sales@coilcraft.com.cn  
**Singapore** + 65-6484 8412 sales@coilcraft.com.sg

Document 1644-1 Revised 10/21/24

© Coilcraft Inc. 2024

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.



# Coupled Inductors – MSD1038V Series

| Part number <sup>1</sup> | Inductance <sup>2</sup> (μH) | DCR max <sup>3</sup> (Ohms) | SRF typ <sup>4</sup> (MHz) | Coupling coefficient typ | Leakage Inductance <sup>5</sup> typ (μH) | Isolation <sup>6</sup> (Vrms) | Isat <sup>7</sup> (A) | Irms (A) <sup>8</sup> |             |
|--------------------------|------------------------------|-----------------------------|----------------------------|--------------------------|--|-------------------------------|-----------------------|-----------------------|-------------|
|                          |                              |                             |                            |                          |  |                               |                       | both windings         | one winding |
| MSD1038V-103ME           | 10 ±20%                      | 0.108                       | 26.0                       | ≥0.95                    | 0.5                                      | 2250                          | 4.7                   | 2.75                  | 3.90        |
| MSD1038V-223ME           | 22 ±20%                      | 0.240                       | 16.5                       | ≥0.96                    | 0.7                                      | 2250                          | 3.1                   | 1.30                  | 1.80        |
| MSD1038V-333ME           | 33 ±20%                      | 0.340                       | 13.0                       | ≥0.96                    | 0.8                                      | 2250                          | 2.6                   | 1.00                  | 1.45        |
| MSD1038V-473ME           | 47 ±20%                      | 0.460                       | 11.0                       | ≥0.96                    | 0.9                                      | 2250                          | 2.2                   | 0.92                  | 1.30        |
| MSD1038V-683ME           | 68 ±20%                      | 0.690                       | 9.0                        | ≥0.96                    | 1.0                                      | 2250                          | 1.8                   | 0.78                  | 1.10        |
| MSD1038V-104ME           | 100 ±20%                     | 0.950                       | 7.5                        | ≥0.96                    | 1.2                                      | 2250                          | 1.5                   | 0.67                  | 0.95        |
| MSD1038V-124ME           | 120 ±20%                     | 1.150                       | 6.8                        | ≥0.96                    | 1.3                                      | 2250                          | 1.3                   | 0.53                  | 0.75        |
| MSD1038V-154ME           | 150 ±20%                     | 1.350                       | 6.0                        | ≥0.96                    | 1.5                                      | 2250                          | 1.2                   | 0.46                  | 0.65        |

1. When ordering, please specify **termination** and **packaging** codes:

## MSD1038V-154KEC

**Termination:** E = RoHS compliant matte tin over nickel over phos bronze. Special order: Q = RoHS tin-silver-copper (95.5/4/0.5) or P = non-RoHS tin-lead (63/37).

**Packaging:** C = 7" machine-ready reel. EIA-481 embossed plastic tape. (250 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (1000 parts per full reel)

- Inductance shown for each winding, measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent. When leads are connected in parallel, inductance is the same value. When leads are connected in series, inductance is four times the value.
- DCR is for each winding.
- SRF measured using an Agilent/HP 4191A or equivalent. When leads are connected in parallel, SRF is the same value.
- Leakage Inductance is for L1 and is measured with L2 shorted.
- 2250 Vrms, one minute isolation (hipot) between windings.
- DC current, at which the inductance drops 30% (typ) from its value without current. It is the sum of the current flowing in both windings.
- Current that causes a 40°C temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

**Core material** Ferrite

**Weight:** 1.2– 1.5 g

**Environmental** RoHS compliant, halogen free

**Terminations** RoHS compliant matte tin over nickel over phos bronze. Other terminations available at additional cost.

**Ambient temperature** –40°C to +125°C with Irms current.

**Maximum part temperature** +165°C (ambient + temp rise).

**Storage temperature** Component: –40°C to +165°C.

Tape and reel packaging: –40°C to +80°C

**Winding-to-winding isolation** 2250 Vrms, one minute

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)


**Packaging** 250/7" reel; 1000/13" reel Plastic tape: 24 mm wide, 0.35 mm thick, 16 mm pocket spacing, 4.3 mm pocket depth

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).


## Coupled Inductor Core and Winding Loss Calculator

This web-based utility allows you to enter frequency, peak-to-peak (ripple) current, and Irms current to predict temperature rise and overall losses, including core loss. [Go to online calculator.](#)

## Typical L vs Current



## Typical L vs Frequency



[www.coilcraft.com](http://www.coilcraft.com)

US +1-847-639-6400 [sales@coilcraft.com](mailto:sales@coilcraft.com)  
 UK +44-1236-730595 [sales@coilcraft-europe.com](mailto:sales@coilcraft-europe.com)  
 Taiwan +886-2-2264 3646 [sales@coilcraft.com.tw](mailto:sales@coilcraft.com.tw)  
 China +86-21-6218 8074 [sales@coilcraft.com.cn](mailto:sales@coilcraft.com.cn)  
 Singapore + 65-6484 8412 [sales@coilcraft.com.sg](mailto:sales@coilcraft.com.sg)

Document 1644-2 Revised 10/21/24

© Coilcraft Inc. 2024

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.