


# Flyback Transformer For Freescale Semiconductor MC34670 PD Interface



- Designed for 13 W IEEE 802.3af-compliant PoE applications
- Operates with 36–80 Volts input
- 1500 Vrms isolation between the primary and the secondary

# Core material Ferrite

**Terminations** RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 6.3 g

Ambient temperature -40°C to +85°C

**Storage temperature** Component: -40°C to +85°C. Packaging: -40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

**Packaging** 175 per 13" reel Plastic tape: 32 mm wide, 0.5 mm thick, 28 mm pocket spacing, 12.93 mm pocket depth **PCB washing** Only pure water or alcohol recommended

Part	Power	Inductance at 0 A <sup>2</sup>		DCR max (Ohms) <sup>4</sup>			Leakage	<b>Turns</b>	Turns ratio <sup>6</sup>		
number <sup>1</sup>	(W)	±10% (μΗ)	min (µH)	pri	bias	sec	max (µH)	pri : sec	pri : bias	(A)	Output <sup>7</sup>
DA2362-AL_	13	127	114.3	0.222	0.405	0.039	0.950	1:0.250	1:0.594	1.0	5 V, 2.6 A

1. When ordering, please specify packaging code:


#### DA2362-ALD


- Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (175 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
  - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.
- 2. Inductance is for the primary, measured at 250 kHz, 0.2 Vrms, 0 Adc.
- 3. Peak primary current drawn at minimum input voltage.
- 4. DCR for the secondary is per winding.
- 5. Leakage inductance measured between pins 3 and 4 with secondary pins shorted.
- 6. Turns ratio is with the secondary windings connected in parallel.


Output of the secondary is with the windings connected in parallel. Bias winding output is 12 V, 20 mA.

8. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.









Dimensions are in  $\frac{\text{inches}}{\text{mm}}$ 

Specifications subject to change without notice. Please check our website for latest information



## US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg





## Document 563 Revised 12/13/21

© Coilcraft Inc. 2021

This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information