NEW!

Shielded Coupled Inductors MSD1583T


RoHS/ REACH COMPLIANT

Halogen Free


AEC Q200 +125°C




- Excellent coupling coefficient (k ≥ 0.98)
- Ideal for use in a variety of circuits including flyback, multi-output buck, SEPIC, Zeta, and Ćuk.
- High inductance, high efficiency and excellent current handling.
- In SEPIC topologies, the required inductance for each winding is half the value needed for two separate inductors, allowing selection of a part with lower DCR and higher current handling.
- AEC-Q200 qualified




Dimensions are in inches / mm



Typical Flyback Converter



Typical Buck Converter with auxiliary output



Coilcraft®
www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 948-1 Revised 10/30/26

© Coilcraft Inc. 2026
This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

RoHS/ REACH COMPLIANT

Halogen Free

AEC Q200 +125°C

MSD1583T Shielded Coupled Inductors for SEPIC applications

Part number[1]	Inductance[2] (µH)	DCR (Ohms)[3] typ	DCR (Ohms)[3] max	SRF typ[4] (MHz)	Coupling coefficient typ	Leakage inductance typ (µH)	Isat (A)[5] 10% drop	Isat (A)[5] 20% drop	Isat (A)[5] 30% drop	Irms (A) both windings[6]	Irms (A) one winding[7]
MSD1583T-103MED	10 ±20%	0.026	0.031	16.0	0.98	0.33	11.7	13.3	14.5	3.68	5.20
MSD1583T-123MED	12 ±20%	0.029	0.037	14.5	0.98	0.36	10.6	12.1	13.2	3.54	5.00
MSD1583T-153MED	15 ±20%	0.039	0.045	12.0	0.99	0.38	9.50	10.8	11.8	3.18	4.50
MSD1583T-183MED	18 ±20%	0.042	0.048	11.5	0.99	0.40	8.70	9.90	10.8	3.04	4.30
MSD1583T-223MED	22 ±20%	0.054	0.065	10.5	0.99	0.40	7.90	8.95	9.80	2.44	3.45
MSD1583T-333MED	33 ±20%	0.083	0.095	8.0	0.99	0.54	6.40	7.30	8.00	2.16	3.05
MSD1583T-473MED	47 ±20%	0.100	0.115	7.1	0.99	0.46	5.40	6.10	6.70	1.98	2.80
MSD1583T-683MED	68 ±20%	0.145	0.165	5.7	0.99	0.79	4.50	5.10	5.50	1.56	2.20
MSD1583T-104KED	100 ±10%	0.230	0.260	5.1	>0.99	0.59	3.70	4.20	4.60	1.24	1.75
MSD1583T-154KED	150 ±10%	0.340	0.380	3.7	>0.99	0.70	3.00	3.42	3.75	1.06	1.50
MSD1583T-224KED	220 ±10%	0.420	0.460	3.2	>0.99	0.89	2.50	2.83	3.10	0.92	1.30
MSD1583T-474KED	470 ±10%	0.950	1.04	2.2	>0.99	1.16	1.70	1.93	2.12	0.65	0.92
MSD1583T-105KED	1000 ±10%	2.20	2.40	1.6	>0.99	2.02	1.17	1.32	1.45	0.42	0.60

1. When ordering, please specify **termination** code:

   MSD1583T-105KED

   Termination: **E** = RoHS compliant matte tin over nickel over phos bronze. Special order: **Q** = RoHS tin-silver-copper (95.5/4/0.5) or **P** = non-RoHS tin-lead (63/37).


   Packaging: **D** = 13″ machine-ready reel. EIA-481 embossed plastic tape (300 parts per full reel).
2. Inductance shown for each winding, measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent. When leads are connected in parallel, inductance is the same value. When leads are connected in series, inductance is four times the value.
3. DCR is for each winding. When leads are connected in parallel, DCR is half the value. When leads are connected in series, DCR is twice the value.
4. SRF measured using an Agilent/HP 4191A or equivalent. When leads are connected in parallel, SRF is the same value.
5. DC current at which the inductance drops the specified amount from its value without current. It is the sum of the current flowing in both windings.
6. Equal current when applied to each winding simultaneously that causes a 40°C temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. To predict temperature rise go to online calculator.
7. Maximum current when applied to one winding that causes a 40°C temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. o predict temperature rise go to online calculator.
8. Electrical specifications at 25°C.

Refer to Doc 639 “Selecting Coupled Inductors for SEPIC Applications.”
Refer to Doc 362 “Soldering Surface Mount Components” before soldering.


Coupled Inductor Core and Winding Loss Calculator

This web-based utility allows you to enter frequency, peak-to-peak (ripple) current, and Irms current to predict temperature rise and overall losses, including core loss. Go to online calculator.

Typical L vs Current



Typical L vs Frequency



Coilcraft®
www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 948-2 Revised 10/30/26

© Coilcraft Inc. 2026
This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

MSD1583T Shielded Coupled Inductors for Flyback applications

Part number[1]	Inductance at 0 A[2] (µH)	Inductance at Ipk A[3] typ (µH)	DCR max (Ohms)	Leakage inductance[4] typ (µH)	Turns ratio	Isat[3] (A)
MSD1583T-103MED	10 ±20%	7.0	0.031	0.33	1 : 1	14.5
MSD1583T-123MED	12 ±20%	8.4	0.037	0.36	1 : 1	13.2
MSD1583T-153MED	15 ±20%	10.5	0.045	0.38	1 : 1	11.8
MSD1583T-183MED	18 ±20%	12.6	0.048	0.40	1 : 1	10.8
MSD1583T-223MED	22 ±20%	15.4	0.065	0.40	1 : 1	9.80
MSD1583T-333MED	33 ±20%	23.1	0.095	0.54	1 : 1	8.00
MSD1583T-473MED	47 ±20%	32.9	0.115	0.46	1 : 1	6.70
MSD1583T-683MED	68 ±20%	47.6	0.165	0.79	1 : 1	5.50
MSD1583T-104KED	100 ±10%	70.0	0.26	0.59	1 : 1	4.60
MSD1583T-154KED	150 ±10%	105	0.38	0.70	1 : 1	3.75
MSD1583T-224KED	220 ±10%	154	0.46	0.89	1 : 1	3.10
MSD1583T-474KED	470 ±10%	329	1.04	1.16	1 : 1	2.12
MSD1583T-105KED	1000 ±10%	700	2.4	2.02	1 : 1	1.45

1. When ordering, please specify **termination** code:

MSD1583T-105KED

Termination: E = RoHS compliant matte tin over nickel over phos bronze.
Special order: **Q** = RoHS tin-silver-copper (95.5/4/0.5) or **P** = non-RoHS tin-lead (63/37).

Packaging: D = 13″ machine-ready reel. EIA-481 embossed plastic tape (300 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer ($25 charge).

2. Inductance is for the primary (L1), measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent.
3. DC current that causes the primary inductance drop of 30% (typ) from its value without current.
4. Leakage inductance is for the primary winding (L1) with the secondary winding (L2) shorted.
5. Electrical specifications at 25°C.

Refer to Doc 362 “Soldering Surface Mount Components” before soldering.

Core material Ferrite
Core and winding loss Go to online calculator
Environmental RoHS compliant, halogen free
Terminations RoHS compliant matte tin over nickel over phos bronze. Other terminations available at additional cost.
Weight: 3.7 – 4.4 g
Ambient temperature –40°C to +125°C with (40°C rise) Irms current.
Maximum part temperature +165°C (ambient + temp rise).
Storage temperature Component: –40°C to +165°C.
Tape and reel packaging: –40°C to +80°C
Winding-to-winding isolation 500 Vrms, one minute
Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles
Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)
Packaging 300/13″ reel; Plastic tape: 32 mm wide, 0.5 mm thick, 24 mm pocket spacing, 8.6 mm pocket depth
PCB washing Tested with pure water or alcohol only. For other solvents, see Doc787_PCB_Washing.pdf.

Coilcraft
www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

© Coilcraft Inc. 2026
This product may not be used in medical or high risk applications without prior Coilcraft approval.
Specification subject to change without notice.
Please check web site for latest information.