








Shielded Power Inductors - XFL5030





- Exceptionally low DCR only 2.15 mOhms
- Excellent current handling up to 11.5 A
- AEC-Q200 Grade 1 (-40°C to +125°C)
- 3.1 mm maximum height with a 5.48 mm × 5.28 mm footprint

Core material Composite

Terminations RoHS compliant tin-silver over copper. Other terminations available at additional cost.

Weight 0.42 – 0.50 g

Ambient temperature -40° C to $+125^{\circ}$ C with (40° C rise) Irms current. Operating voltage 0 - 20 V

Maximum part temperature $+165^{\circ}$ C (ambient + temp rise). Derating. Storage temperature Component: -55° C to $+165^{\circ}$ C. Tape and reel packaging: -55° C to $+80^{\circ}$ C

 Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

 Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)</td>

 Packaging 400/7" reel; 1500/13" reel
 Plastic tape: 16 mm wide,

0.3 mm thick, 12 mm pocket spacing, 3.18 mm pocket depth **PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See <u>Doc787</u> PCB Washing.pdf.

	Inductance ²	DCR (mOhms) ³		SRF typ⁴		Isat (A)⁵		Irms (A) ⁶	
Part number ¹	±20% (μH)	typ	max	(MHz)	10% drop	20% drop	30% drop	20°C rise	40°C rise
XFL5030-271ME_	0.27	2.15	2.55	132	10.0	11.0	11.5	18.0	25.5
XFL5030-561ME_	0.56	3.20	3.80	77.0	7.5	8.5	9.0	14.6	21.0
XFL5030-102ME_	1.0	4.20	5.00	60.0	5.4	6.2	6.5	13.0	18.0
XFL5030-222ME_	2.2	10.5	12.0	37.4	3.5	4.0	4.3	8.2	11.5
XFL5030-332ME_	3.3	13.5	16.0	28.7	3.1	4.0	4.2	7.2	10.0
XFL5030-472ME_	4.7	18.5	22.0	24.5	2.5	3.1	3.3	6.2	8.7

1. When ordering, please specify packaging code:

XFL5030-472MEC

- Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (400 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating
 - the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.
 - **D** = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (1500 parts per full reel).
- 2. Inductance tested at 1 MHz, 0.1 Vrms, 0 Adc.
- 3. DCR measured on a micro-ohmmeter.
- 4. SRF measured using Agilent/HP 4395A or equivalent.
- 5. DC current at 25°C that causes an inductance drop of 30% (typ) from its value without current. Click for temperature derating information.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. <u>Click for temperature derating information</u>.
- 7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Irms Testing

Irms testing was performed on 0.75 inch wide $\times 0.25$ inch thick copper traces in still air.

Temperature rise is highly dependent on many factors including pcb land pattern, trace size, and proximity to other components. Therefore temperature rise should be verified in application conditions.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 791-1 Revised 11/24/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information

1.0 μH

0.56 µH


0.27 µH

0.122 max*


3,1

10

100



Shielded Power Inductors - XFL5030



www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 791-2 Revised 11/24/21

© Coilcraft Inc. 2021

0.165 typ

4,2

Dimensions are in inches

* For optional tin-lead and tin-silver-

copper terminations, dimensions are for the mounted part.

Dimensions before mounting can be an additional 0.005 inch / 0.13 mm.

This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information