


Flyback Transformer For Linear Technology LT3751 Capacitor Charger Controller



- Flyback transformer for the Linear Technology LT3751 Capacitor Charger Controller
- 120 377 V input; up to 500 V output
- 3000 Vrms isolation from primary to secondary windings

Core material Ferrite

Terminations RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

Weight 23.8 g

Ambient temperature -40°C to +85°C

Storage temperature Component: -40°C to +85°C.

Tray packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 24 per tray

PCB washing Tested with pure water or alcohol only. For other solvents, see Doc787_PCB_Washing.pdf.


Part	Inductance at 0 A ¹	Inductance at Ipk ²	DCR max (Ohms) ³		Leakage inductance ⁴	Turns ratio ⁵	Ipk ²	Volt-time product
number	±10%(µH)	min (μH)	pri	sec	max (µH)	pri:sec	(A)	typ (V µsec)
HA4060-AL	300	270	0.422	1.58	2.7	1:3	2.0	600

- 1. Inductance is measured at 100 kHz, 0.1 Vrms.
- 2. Peak primary current drawn at minimum input voltage.


1.024 26,0 1.350 max

- 3. DCR is with the windings connected in parallel.
- 4. Leakage inductance is for both windings of the primary with the secondary windings shorted.
- 5. Turns ratios are with the primary and secondary windings connected in
- 6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



□ 0.004 / 0,10



Primary windings and secondary windings to be connected in parallel on PC board.



US +1-847-639-6400 sales@coilcraft.com **UK** +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw **China** +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Dimensions are in

Document 734 Revised 11/23/21

© Coilcraft Inc. 2021

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice.
Please check web site for latest information.