

Common Mode Chokes – MSD1278



- Only 12.3 mm square and 8 mm high
- Ideal for use in both power line and signal line applications
- Common- and differential-mode filtering in a single device
- Up to 110 MHz differential mode cutoff frequency
- 500 Vrms, one minute winding-to-winding isolation
- Can be used as coupled inductors for SEPIC applications

Core material Ferrite

Weight: 3.7 – 4.4 g

Terminations RoHS compliant matte tin over nickel over phos bronze. Other terminations available at additional cost.

Ambient temperature –40°C to +85°C with Irms current.

Maximum part temperature +125°C (ambient + temp rise).

Storage temperature Component: –40°C to +125°C.

Tape and reel packaging: –40°C to +80°C



Winding-to-winding isolation 500 Vrms, one minute

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles


Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 500/13" reel; Plastic tape: 24 mm wide, 0.5 mm thick, 16 mm pocket spacing, 8.7 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).




Recommended Land Pattern



* For optional tin-lead and tin-silver-copper terminations, dimensions are for the mounted part. Dimensions before mounting can be an additional 0.012 inch (0,3 mm).

Dimensions are in $\frac{\text{inches}}{\text{mm}}$





Common Mode Chokes – MSD1278 Series

| Partnumber ¹ | Common mode impedance max (kOhms) | Cutoff ² frequency (MHz) | Inductance (μH) ³ | | DCR max ⁴ (Ohms) | Isolation (Vrms) | Irms (A) |
|-------------------------|-----------------------------------|-------------------------------------|------------------------------|------|-----------------------------|------------------|----------|
| | | | min | nom | | | |
| MSD1278-472ML_ | 7.74 @ 32 MHz | 110 | 3.76 | 4.7 | 0.038 | 500 | 3.16 |
| MSD1278-562ML_ | 7.70 @ 25 MHz | 81 | 4.48 | 5.6 | 0.046 | 500 | 2.87 |
| MSD1278-682ML_ | 9.71 @ 22 MHz | 63 | 5.44 | 6.8 | 0.048 | 500 | 2.81 |
| MSD1278-822ML_ | 10.77 @ 21 MHz | 87 | 6.56 | 8.2 | 0.050 | 500 | 2.76 |
| MSD1278-103ML_ | 11.29 @ 19 MHz | 58 | 8.00 | 10 | 0.058 | 500 | 2.56 |
| MSD1278-123ML_ | 13.41 @ 17 MHz | 57 | 9.60 | 12 | 0.062 | 500 | 2.48 |
| MSD1278-153ML_ | 17.44 @ 16 MHz | 53 | 12.0 | 15 | 0.072 | 500 | 2.30 |
| MSD1278-183ML_ | 16.96 @ 15 MHz | 43 | 14.4 | 18 | 0.080 | 500 | 2.18 |
| MSD1278-223ML_ | 19.54 @ 12 MHz | 35 | 17.6 | 22 | 0.096 | 500 | 1.99 |
| MSD1278-273ML_ | 22.40 @ 11 MHz | 39 | 21.6 | 27 | 0.12 | 500 | 1.78 |
| MSD1278-333ML_ | 39.00 @ 9.8 MHz | 37 | 26.4 | 33 | 0.15 | 500 | 1.59 |
| MSD1278-393ML_ | 47.17 @ 9.0 MHz | 42 | 31.2 | 39 | 0.16 | 500 | 1.54 |
| MSD1278-473ML_ | 48.28 @ 8.6 MHz | 28 | 37.6 | 47 | 0.18 | 500 | 1.45 |
| MSD1278-563ML_ | 55.35 @ 7.7 MHz | 26 | 44.8 | 56 | 0.19 | 500 | 1.41 |
| MSD1278-683ML_ | 63.59 @ 6.8 MHz | 22 | 54.4 | 68 | 0.21 | 500 | 1.35 |
| MSD1278-823ML_ | 76.76 @ 6.1 MHz | 22 | 65.6 | 82 | 0.28 | 500 | 1.16 |
| MSD1278-104ML_ | 79.30 @ 5.8 MHz | 22 | 80.0 | 100 | 0.30 | 500 | 1.13 |
| MSD1278-124KL_ | 95.79 @ 4.9 MHz | 18 | 108 | 120 | 0.41 | 500 | 0.96 |
| MSD1278-154KL_ | 80.01 @ 4.3 MHz | 23 | 135 | 150 | 0.46 | 500 | 0.91 |
| MSD1278-184KL_ | 82.56 @ 3.9 MHz | 13 | 162 | 180 | 0.51 | 500 | 0.86 |
| MSD1278-224KL_ | 114.9 @ 3.7 MHz | 13 | 198 | 220 | 0.69 | 500 | 0.74 |
| MSD1278-274KL_ | 140.0 @ 2.9 MHz | 12 | 243 | 270 | 0.90 | 500 | 0.65 |
| MSD1278-334KL_ | 101.7 @ 2.8 MHz | 9.4 | 297 | 330 | 1.02 | 500 | 0.61 |
| MSD1278-394KL_ | 87.12 @ 2.6 MHz | 9.4 | 351 | 390 | 1.12 | 500 | 0.58 |
| MSD1278-474KL_ | 159.6 @ 2.3 MHz | 11 | 423 | 470 | 1.43 | 500 | 0.50 |
| MSD1278-564KL_ | 142.6 @ 2.2 MHz | 8.7 | 504 | 560 | 1.69 | 500 | 0.47 |
| MSD1278-684KL_ | 165.0 @ 1.9 MHz | 7.4 | 612 | 680 | 2.29 | 500 | 0.41 |
| MSD1278-824KL_ | 138.0 @ 1.8 MHz | 6.9 | 738 | 820 | 2.55 | 500 | 0.39 |
| MSD1278-105KL_ | 154.0 @ 1.7 MHz | 6.0 | 900 | 1000 | 2.83 | 500 | 0.37 |

1. When ordering, please specify **termination** and **packaging** code:

MSD1278-105KLD

Termination: L = RoHS compliant matte tin over nickel over phos bronze

Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or S = non-RoHS tin-lead (63/37).

Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (500 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.

2 Frequency at which the differential mode attenuation equals -3 dB

3 Inductance shown for each winding, measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent.

4 DCR is for each winding.

5 Interwinding isolation (hipot) tested for one minute.

6 Current that causes a 40°C temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.


9. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.




Common Mode Chokes – MSD1278 Series

Typical Attenuation (Ref: 50 Ohms)



Typical Impedance vs Frequency



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1332-3 Revised 02/16/22

© Coilcraft Inc. 2022

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.