


Bias Injection Choke – KA4909-AL



Developed for use with Texas Instruments DS90UB901Q serializer and DS90UB902Q deserializer for Low-Voltage Differential Signaling (LVDS) applications.

This center tapped inductor provides over 1 kOhm impedance from 1 MHz – 800 MHz.

Can be used with additional 10 μ H and 1 μ H inductors to achieve even wider band differential signal rejection.

AEC-Q200 Grade 3 (–40°C to +85°C) qualified

Core material Ferrite

Terminations RoHS compliant tin-silver-copper over tin over nickel over phos bronze.

Weight 220 mg

Ambient temperature –40°C to +105°C

Storage temperature Component: –40°C to +105°C.

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

60 per billion hours / 16,666,667 hours, calculated per Telcordia SR-332

Packaging 250/7" reel; 1000/13" reel Plastic tape: 16 mm wide, 0.35 mm thick, 12 mm pocket spacing, 5.0 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Inductance ² $\pm 25\%$ (μ H)	DCR max ³ (Ohms)	Irms ⁴ (mA)
KA4909-AL_	169	0.46	650

1. When ordering, please specify **packaging** code:

KA4909-ALC

Packaging: **C** = 7" machine ready reel. EIA-481 embossed plastic tape, 250 parts per full reel.

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter C instead.

D = 13" machine ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (1000 parts per full reel).






2. Inductance tested from pins 1 to 3 at 100 kHz, 0.007 Vrms, 0 Adc.

3. DCR is tested from pins 1 to 3

4. Current that causes a 20°C rise from 25°C ambient.


5. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Dimensions are in inches / mm

Impedance vs Frequency



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 992 Revised 11/18/16

© Coilcraft Inc. 2016

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.