


NEW!

High Current Ferrite Beads – SLZ4040



- Wirewound surface mount package
- High current ferrite beads designed for high frequency EMI noise cancellation
- Optimized for CISPR 25 EMC compliance, 30 MHz to 3 GHz
- AEC-Q200 Qualified

Core material Ferrite

Environmental RoHS compliant, halogen free

Terminations RoHS compliant matte tin over nickel over copper.

Weight 0.24 – 0.26 g

Ambient temperature –40°C to +105°C with (40°C rise) Irms current.

Maximum part temperature +145°C (ambient + temp rise).

Storage temperature Component: –40°C to +105°C.

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 500/7" reel; 2000/13" reel; Plastic tape: 12 mm wide, 0.35 mm thick, 8 mm pocket spacing, 4.0 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Part number ¹	Impedance typ (Ohms)		Inductance ² ±20% (nH)	DCR ±10% ³ (mOhms)	Isat ⁴ (A)	Irms (A) ⁵	
	100 MHz	1 GHz				20°C rise	40°C rise
SLZ4040-180MEC	18	78	30	0.32	46	32	44
SLZ4040-350MEC	35	74	80	0.32	16	32	44

1. When ordering, please specify **packaging** code:


SLZ4040-350MEC

Packaging: **C** = 7" machine-ready reel. EIA-481 embossed plastic tape (500 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

D = 13" machine-ready reel. EIA-481 embossed plastic tape (2000 parts per full reel). Factory order only, not stocked.

2. Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc.

3. DCR is measured on a micro-ohmmeter at points indicated in the diagram below.





▲Points used for measuring DCR

4. DC current that causes an inductance drop of 20% (typ) from its value without current.



5. Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. Temperature rise is highly dependent on many factors including pcb land pattern, trace size, air flow, and proximity to other components. Therefore temperature rise should be verified in application conditions. [Click for temperature derating information.](#)

6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Dimensions are in inches/mm





Recommended Land Pattern





SLZ4040 High Current Ferrite Beads

L vs Current vs Temperature



Impedance vs Frequency



US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1892-2 Revised 05/28/26
 © Coilcraft Inc. 2026
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.