




# Flyback Transformer

For Texas Instruments  
LM5071 PoE PD Controller



- Designed to operate in continuous mode at 250 kHz
- TI App Note AN-1430 specifies 84% efficiency at 3 A.
- 1500 Vrms, one minute isolation from primary and aux to secondary

**Core material** Ferrite

**Terminations** RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

**Weight** 5.97 g

**Ambient temperature** -40°C to +85°C

**Storage temperature** Component: -40°C to +85°C.  
Tape and reel packaging: -40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Packaging** 175 per 13" reel Plastic tape: 32 mm wide, 0.5 mm thick

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787\\_PCB\\_Washing.pdf](#).

Part number <sup>1</sup>	L at 0 A <sup>2</sup> ±10% (µH)	L at Ipk <sup>3</sup> min (µH)	Input voltage (V)	DCR max (Ohms)	Leakage L <sup>4</sup> max (µH)	Turns ratios	Ipk <sup>3</sup> (A)	Outputs <sup>5</sup>
DA2383-AL_	127.0	114.3	24 -60	0.310 (aux) 0.012 (sec) 0.255 (pri)	1.25	2 : 1 (pri : aux) 6 : 1 (pri : sec )	1.0	10 V, 0.05 A (aux) 3.3 V, 4.0 A (sec)


1. When ordering, please specify **packaging** code:

**DA2383-ALD**



**Packaging:** D = 13" machine-ready reel. EIA-481 embossed plastic tape (175 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

B= Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.

2. Inductance is for the primary, measured at 200 kHz, 0.2 Vrms, 0 Adc.
  3. Ipk is peak primary current drawn at minimum input voltage.
  4. Leakage inductance measured on the primary winding with all secondary pins shorted.
  5. Output of the secondary is with the windings connected in parallel.
  6. Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Dimensions are in inches mm



Secondary windings to be connected in parallel on the PCB board



**US** +1-847-639-6400 sales@coilcraft.com  
**UK** +44-1236-730595 sales@coilcraft-europe.com  
**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw  
**China** +86-21-6218 8074 sales@coilcraft.com.cn  
**Singapore** + 65-6484 8412 sales@coilcraft.com.sg

Document 523 Revised 10/29/08

© Coilcraft Inc. 2021

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.