







Shielded Power Inductors – SLR1075



- Tight DCR tolerance for inductor-DCR-based current sensing circuits
- Excellent current handling, up to 93 A
- $10.4 \times 8.0 \times 7.4$ mm surface mount package
- Designed for use in multi-phase VRM/VRD/EVRD regulators

Designer's Kit C467 contains 3 each of select values. Core material Ferrite Weight 3.5 – 3.6 g Environmental RoHS compliant, halogen free Terminations RoHS compliant matte tin over nickel over copper. Ambient temperature -40°C to +85°C with (40°C rise) Irms current. Maximum part temperature +125°C (ambient + temp rise). Storage temperature Component: -40°C to +125°C. Tape and reel packaging: -40°C to +80°C Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity) Declering 100/27 mode E00(127 mode E00(127 mode).

Packaging 100/7" reel; 500/13" reel; Plastic tape: 24 mm wide, 0.4 mm thick, 12 mm pocket spacing, 7.75 mm pocket depth **PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.

Irms testing was performed on 0.75 inch wide \times 0.25 inch thick

Temperature rise is highly dependent on many factors including

pcb land pattern, trace size, and proximity to other components.

Therefore temperature rise should be verified in application

	Inductance ²	DCR ±7% ³	SRF typ	Isat (A) ⁴			Irms (A) ⁵	
Part number ¹	±10% (nH)	(mOhms)	(MHz)	at 25°C	at 100°C	at 125°C	20°C rise	40°C rise
SLR1075-121KE_	120	0.29	59	93.0	78.5	72.0	50	67
SLR1075-151KE_	150	0.29	48	72.0	59.0	54.0	50	67
SLR1075-171KE_	170	0.29	44	65.0	51.5	48.0	50	67
SLR1075-221KE_	215	0.29	36	53.0	40.0	37.0	50	67
SLR1075-231KE_	230	0.29	35	49.0	36.5	33.5	50	67
SLR1075-271KE_	270	0.29	30	41.0	32.0	29.5	50	67
SLR1075-301KE_	300	0.29	27	36.0	26.5	24.0	50	67

Irms Testing

conditions.

copper traces in still air.

1. When ordering, please specify **packaging** code:

SLR1075-301KEC

- Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (100 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.
 - D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (500 parts per full reel).
- 2. Inductance at 100 kHz, 0.1 Vrms, 0 Adc.
- 3. DCR is measured on a micro-ohmmeter at points indicated in the diagram below.



- 4. DC current that causes an inductance drop of 20% (typ) from its value without current.
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings.
- 6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1306-1 Revised 07/06/23


© Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.


3.2



laloge

SLR1075 Shielded Power Inductors









US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg Document 1306-2 Revised 07/06/23


© Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information





SLR1075 Shielded Power Inductors











360



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg

Document 1306-3 Revised 07/06/23

© Coilcraft Inc. 2023

This product may not be used in medical or high risk applications without prior Collcraft approval Specification subject to change without notice Please check web site for latest information