








## Backlight Inductors – DO1607B Series





Part number <sup>1</sup>	L <sup>2</sup> ±20% (mH)	DCR <sup>3</sup> max (Ohms)	Insulation core-winding (MOhms)	Isat <sup>4</sup> (mA)	Irms⁵ (mA)
DO1607B-105ML_	1.0	19	>10	100	150
DO1607B-155ML_	1.5	21	>10	75	140
DO1607B-225ML_	2.2	42	>10	60	100
DO1607B-335ML_	3.3	52	>10	50	90
DO1607B-475ML_	4.7	80	>10	45	75
DO1607B-685ML_	6.8	125	>10	40	60

1. When ordering, please specify termination and packaging codes:

## DO1607B-685MLC

Termination: L = RoHS compliant electroplated gold (<50 μin) over nickel over moly-manganese. Special order: T = RoHS tin-silver-copper (95.5/4/0.5)

or  $\mathbf{S}$  = non-RoHS tin-lead (63/37).

- Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (750 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
  - $\mathbf{D}$  = 13" machine-ready reel. EIA-481 embossed plastic tape (2500 parts per full reel).
  - B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.
- 2. Inductance tested at 0.1 Vrms, 100 kHz, 0 Adc on Agilent/HP 4192A.
- 3. DCR tested on Cambridge Technology 510-A with Coilcraft CCF-859 fixture.
- DC current at which the inductance drops 10% (typ) from its value without current.
- 5. Average current for a 40°C rise above 25°C ambient.
- 6. Operating temperature -40°C to +85°C.
- 7. Electrical specifications at 25°C.


Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

The low profile DO1607B Series has the high breakdown voltage ratings required for backlight applications. Only 2,49 mm high, they have a footprint of  $6,6 \times 4,5$  mm.

These inductors are constructed of high temperature materials that provide excellent heat deflection to prevent damage during solder reflow. Standard inductance values range from 1 to 6.8 mH and custom values are available to meet specific requirements.

Coilcraft **Designer's Kit C335** contains samples of each of the standard parts shown. To order, contact Coilcraft or visit **http://order.coilcraft.com**.

## Typical Inductance vs. Current



**Weight:** 0.12 – 0.13 g

 Tape and reel:
 750/7" reel; 2500/13" reel
 Plastic tape:
 12 mm wide,

 0.28 mm thick, 8 mm pocket spacing, 3.0 mm pocket depth

 PCB washing
 Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787\_PCB\_Washing.pdf.



 US
 +1-847-639-6400
 sales@coilcraft.com

 UK
 +44-1236-730595
 sales@coilcraft-europe.com

 Taiwan
 +886-2-2264
 3646
 sales@coilcraft.com.tw

 China
 +886-21-6218
 8074
 sales@coilcraft.com.cn

 Singapore
 + 65-6484
 8412
 sales@coilcraft.com.sg

## Document 204 Revised 01/24/05

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information.