


Flyback Transformers For Texas Instruments LM5070 PoE Interface – 13 Watt



- Flyback transformers for 13 W PoE applications
- Designed to operate in continuous mode at 250 kHz with an input of 36-72 Vdc
- 1500 Vrms isolation from primary and bias to secondary

Core material Ferrite

Terminations RoHS tin-silver (96.5/3.5) over tin over nickel over phos bronze. Other terminations available at additional cost.

Ambient temperature -40°C to +85°C

Storage temperature Component: -40°C to +85°C.

Tape and reel packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 175 per 13" reel Plastic tape: 32 mm wide, 0.5 mm thick, 28 mm pocket spacing, 12.93 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See Doc787_PCB_Washing.pdf.


Part	Inductance at 0 A ²	Inductance at Ipk ³	DCR max (Ohms)4			Leakage inductance			Ipk ³	
number ¹	±10% (μΗ)	min (μH)	pri	bias	sec	max (µH)⁵	pri:sec	pri : bias	(A)	Output ⁷
C1495-AL_	127	114.3	0.255	0.310	0.024	1.25	1:0.166	1:0.50	1.0	3.3 V, 4.0 A
C1585-AL_	127	114.3	0.222	0.348	0.039	0.950	1:0.25	1:0.50	1.0	5.0 V, 2.6 A
C1586-AL_	127	114.3	0.199	0.308	0.129	0.650	1:0.50	1:0.50	1.0	12 V, 1.08 A

1. When ordering, please specify packaging code:


C1586-ALD

- Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape (175 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - B = Less than full reel. In an effort to simplify our part numbering system, Collcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to D.
- 2. Inductance is for the primary, measured at 250 kHz, 0.2 Vrms, 0 Adc.
- 3. Ipk is peak primary current drawn at minimum input voltage.
- 4. DCR for the secondary is per winding.
- 5. Leakage inductance measured between pins 3 and 4 with all other
- 6. Turns ratio is with the secondary windings connected in parallel.
- Output of the secondary is with the windings connected in parallel. Bias winding output is 12 V, 20 mA.
- 8. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



US +1-847-639-6400 sales@coilcraft.com **UK** +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw **China** +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg



Secondary windings to be connected in parallel on the PC board

Document 445 Revised 07/23/21

© Coilcraft Inc. 2021 This product may not be used in medical or high risk applications without prior Coilcraft approval Specification subject to change without notice Please check web site for latest information

