


Isolation Transformers

For Analog Devices ADuM347x **Quad-Channel Digital Isolators**



- Developed to work with Analog Devices ADuM347x guadchannel, digital isolators with integrated PWM controller and transformer driver
- · Power rating: 2 Watts
- Designed to meet UL/CSA/IEC 60950-1 and 62638-1 Basic Insulation with 1.5 mm creepage and clearance.

Core material Ferrite

Terminations Tin-silver over tin over nickel over phos bronze

Isolation 2500 Vrms primary to secondary; 500 Vrms winding to core Weight 0.95 - 0.98 g

Ambient temperature -40°C to +125°C

Storage temperature Component: -40°C to +125°C.

Tape and reel packaging: -40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Packaging 600/13" reel; Plastic tape: 24 mm wide, 0.37 mm thick, 16 mm pocket spacing, 6.1 mm pocket depth

PCB washing Tested with pure water or alcohol only. For other solvents, see Doc787_PCB_Washing.pdf


				Pri / output voltages				max	Leakage	Volt-time
Part	Inductance ²	Turns		output	output	output		ms) ³	inductance4	product⁵
number ¹	min (µH)	ratio	pri	(pin 8)	(pins 6 & 7)	(pin 5)	pri	sec	max (µH)	(V-µsec)
JA4631-BL_	63.75	1:2	5 V	+3.3 to +5 V	0 V	No output	0.095	0.190	0.460	17.6
JA4650-BL_	63.75	1:3	5 V	+12 to +15 V	+6 to +7.5 V	0 V	0.122	0.260	0.660	17.6
KA4976-AL_	63.75	1:5	5 V	+12 to +15 V	0 V	-12 to -15 V	0.095	1.17	0.515	17.6

1. When ordering, please specify a packaging code:

JA4631-BLD


- Packaging: D = 13" machine ready reel. EIA-481 embossed plastic tape (600 per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).
 - **B** = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.
- 2. Inductance is for the primary, measured from pins 4-3 at 1 kHz, 0.1 Vrms.
- 3. DCR is for each winding of the primary and secondary.
- 4. Leakage inductance is for the primary windings, measured from pins 1-4 with all secondary windings shorted.
- 5. Based on Bsat of the core at 25°C and the number of turns on winding 4-3.
- 6. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Primary windings and secondary windings to be connected in series on the PC board.

Analog Devices is a trademark of Analog Devices, Inc.





US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg Document 888 Revised 04/12/22

© Coilcraft Inc. 2022

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information