SPICE Model – LPS3314


This lumped-element (SPICE) model data simulates the frequency-dependent behavior of Coilcraft power inductors within the frequency range shown in the accompanying table for each individual inductor.

The data represents de-embedded measurements, as described below. Effects due to different customer circuit board traces, board materials, ground planes or interactions with other components are not included and can have a significant effect when comparing the simulation to measurements of the inductors using other production verification instruments and fixtures.

Lumped Element Modeling Method

Measurements were made using a 50 Ohm impedance analyzer. Fixture compensation was performed to remove fixture effects. No DC bias current was applied in any of the measurements. The lumped element values were determined by optimizing the simulation model to an average of the measurements. This method results in a model that represents as closely as possible the typical frequency-dependent behavior of the component within the model frequency range.

The equivalent lumped element model schematic is shown below. Each model should only be analyzed at the input and output ports. Individual elements of the model are not determined by parameter measurement. The elements are determined by the overall performance of the lumped element model compared to the measurements taken of the component.



The value of the frequency-dependent variable resistor $\mathsf{R}_{\mathsf{VAR1}}$ is calculated from:

$$R_{VAR1} = k1 \times \sqrt{f}$$

- k1is shown for each value in the accompanying table.
- f is the frequency in Hz
- R_{VAR1} is the resistance in Ohms

The value of the frequency-dependent variable resistor R_{VAR2} is calculated from:

$$R_{VAR2} = k2 \times \sqrt{f}$$

- k2isshown for each value in the accompanying table.
- f is the frequency in Hz
- R_{VAR2} is the resistance in Ohms

Note: The log function in the following equation is the natural logarithm, base *e*, not base 10.

The value of the frequency-dependent inductance L_{VAR} is calculated from:

$$L_{VAR} = k3 - k4 \times LOG (k5 \times f)$$

- k3, k4, and k5 are shown in the accompanying table.
- f is the frequency in Hz
- L_{VAR} is the inductance in μH
- LOG is the natural LOG (base e)

Disclaimer

Coilcraft makes every attempt to provide accurate measurement data and software, representative of our components, in a usable format. Coilcraft, however, disclaims all warrants relating to the use of its data and software, whether expressed or implied, including without limitation any implied warranties of merchantability or fitness for a particular purpose. Coilcraft cannot and will not be liable for any special, incidental, consequential, indirect or similar damages occurring with the use of the data and/or software.



US +1-847-639-6400 sales@coilcraft.com UK +44-1236-730595 sales@coilcraft-europe.com Taiwan +886-2-2264 3646 sales@coilcraft.com.tw China +86-21-6218 8074 sales@coilcraft.com.cn Singapore + 65-6484 8412 sales@coilcraft.com.sg Document 267-1 Revised 11/06/23 © Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.

SPICE Model for LPS3314 Power Inductors

	Frequency limit of model (MHz)					L _{VAR} Coefficients				
Part number	Lower	Upper	R1 (Ω)	R2 (Ω)	C (pF)	k1	k2	k3	k4	k5
LPS3314-102	0.1	100	450	0.055	0.860	2.00E-04	0.30	1.0	0.019	9.50E-06
LPS3314-222	0.1	100	320	0.100	1.01	1.00E-05	0.62	2.2	0.027	9.80E-06
LPS3314-332	0.1	100	315	0.145	0.918	1.00E-05	0.91	3.3	0.036	9.80E-06
LPS3314-472	0.1	100	165	0.175	1.01	2.00E-05	1.28	4.7	0.048	9.90E-06
LPS3314-562	0.1	100	105	0.220	1.19	5.00E-05	1.42	5.6	0.053	9.90E-06
LPS3314-682	0.1	100	225	0.240	1.10	1.00E-05	2.00	6.8	0.075	9.90E-06
LPS3314-822	0.1	100	205	0.270	0.975	2.00E-05	2.32	8.2	0.116	9.95E-06
LPS3314-103	0.1	80	160	0.330	1.18	4.00E-05	2.82	10	0.14	9.95E-06
LPS3314-153	0.1	80	80	0.440	1.33	8.00E-05	4.18	15	0.22	9.95E-06
LPS3314-183	0.1	80	50	0.575	1.35	5.00E-05	4.84	18	0.28	9.95E-06
LPS3314-223	0.1	70	60	0.720	1.40	1.00E-05	6.10	22	0.28	9.95E-06
LPS3314-333	0.1	40	85	0.920	1.48	1.00E-05	9.52	33	0.28	9.95E-06
LPS3314-473	0.1	30	160	1.40	1.49	1.00E-05	14.1	47	0.28	9.98E-06
LPS3314-563	0.1	30	140	1.55	1.47	1.00E-05	16.3	56	0.28	9.98E-06
LPS3314-683	0.1	20	150	1.80	1.69	1.00E-05	20	68	0.31	1.00E-05
LPS3314-823	0.1	20	200	2.00	1.56	1.00E-05	23	82	0.38	1.00E-05
LPS3314-104	0.1	20	220	2.75	1.39	1.00E-05	28	100	0.51	1.00E-05
LPS3314-124	0.1	20	100	3.45	1.99	1.00E-05	34	120	0.91	1.00E-05
LPS3314-154	0.1	10	120	4.10	1.84	1.00E-05	40	150	0.95	1.01E-05
LPS3314-184	0.1	10	300	4.80	1.77	8.00E-05	56	180	1.16	1.01E-05
LPS3314-224	0.1	10	125	6.00	2.04	1.00E-05	68	220	1.53	1.02E-05
LPS3314-334	0.1	10	260	9.30	1.90	1.00E-05	97	330	3.10	1.02E-05
LPS3314-474	0.1	10	130	12.0	2.06	1.00E-05	140	470	3.25	1.05E-05
LPS3314-564	0.1	7	320	14.0	1.87	1.00E-05	160	560	4.18	1.05E-05
LPS3314-684		7	270	18.5	1.89	1.00E-05	215	680	4.70	1.07E-05
LPS3314-824	0.1	7	150	24.0	2.09	1.00E-05	245	820	6.73	1.08E-05



 US
 +1-847-639-6400
 sales@coilcraft.com

 UK
 +44-1236-730595
 sales@coilcraft-europe.com

 Taiwan
 +886-2-2264
 3646
 sales@coilcraft.com.tw

 China
 +86-21-6218
 8074
 sales@coilcraft.com.cn

 Singapore
 + 65-6484
 8412
 sales@coilcraft.com.sg

Document 267-2 Revised 11/06/23 © Coilcraft Inc. 2023 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.